

# Twist-Lock® Devices

## 20 Ampere, 125, 250 Volts and 277 Volts AC

2 Pole, 3 Wire Grounding

### Insulgrip® Connector Bodies and Receptacles



20A 125V  
NEMA L5-20R  
UL/CSA  
1 HP



20A 250V  
NEMA L6-20R  
UL/CSA  
2 HP



20A 277V AC  
NEMA L7-20R  
UL/CSA  
2 HP

## Connector Bodies

### Watertight Safety-Shroud® IP66 SUITABILITY

Description	Cord Dia.	Catalog Number		
Black Valox® housing, white Valox® clamps.	.360"-.930" (9-24)	HBL2313SW	HBL2323SW	HBL2333SW

### Insulgrip® IP20 SUITABILITY

Description	Cord Dia.	Catalog Number		
Black and white nylon.	.360"-.930" (9-24)	HBL2313	HBL2323	HBL2333
Corrosion resistant, yellow nylon.	.360"-.930" (9-24)	HBL23CM13	HBL23CM23	-
All black nylon.	.360"-.930" (9-24)	HBL2313BK	HBL2323BK	-
Cord clamps with removable inserts. All black nylon.	.360"-.930" (9-24)	HBL2313EBK	HBL2323EBK	-

Accessories on page B-51.

### Valise® IP20 SUITABILITY

Description	Cord Dia.	Catalog Number		
Yellow nylon.	.325"-.720" (8.26-18.3)	HBL2313VY	HBL2323VY	-
Black nylon.	.325"-.720" (8.26-18.3)	HBL2313VBK	HBL2323VBK	HBL2333VBK

Accessories on page B-51.

## Receptacles

### Watertight Safety-Shroud®, Back Wired IP66 SUITABILITY

Description	Catalog Number		
Gray Valox® housing and flange.	HBL2310SW	HBL2320SW	HBL2330SW

Accessories on page B-54.

### Safety-Shroud® Twist-Lock®, Back Wired IP20 SUITABILITY

Description	Catalog Number		
Gray Valox® angle housing, one gang.	HBL2310AR	HBL2320AR	HBL2330AR
Gray Valox® surface mounting, one gang.	HBL2310SR	HBL2320SR	HBL2330SR
Gray Valox® semi-flush, two gang.	HBL2310SR2	HBL2320SR2	HBL2330SR2

Accessories on page B-54.

### Single Flush, Back and Side Wired IP20 SUITABILITY


Description	Catalog Number		
Black nylon face.	HBL2310	HBL2320	HBL2330
Blue nylon face.	HBL2310M7	HBL2320M4	-
Isolated ground, orange nylon face.	IG2310	IG2320	-
Corrosion resistant, yellow nylon face.	HBL23CM10	-	-
Ring terminal connection.	HBL2310RT	HBL2320RT	-

Accessories on page B-50.


### Insulgrip® Flanged Receptacles

Description	Catalog Number		
Nylon casing, back wired.	HBL2316	HBL2326	HBL2336

Accessories on page B-50.



HBL2316



HBL2310




HBL2320SR2




HBL2320SR




HBL2323SW



HBL2313



HBL2313VY



HBL2320SW



HBL2320AR

Valox® is a trademark of SABIC Innovative Plastics, acquired from General Electric Company.