



Hubbell SystemOne 4-Inch Core Hole – One-Piece Poke Throughs

All Hubbell SystemOne 4-inch core, one-piece poke-throughs include the sub-plate and cover to simplify your order and reduce installation time. Units are also available with a power junction box installed. The junction box is also available for purchase separately.

| Description | Color | Catalog No. without Junction Box | Catalog No. with Junction Box* |
|--|---|--|---|
| <p>One-Piece 4X4 Poke-Through Assembled-unit includes:</p> <ul style="list-style-type: none"> • Hubbell SystemOne 4X4 floor fitting (S1PT4X4FIT) • 4X4 sub-plate (S1SP4X4) • Finish flange and universal carpet cover assembly (S1CFCxx) • 4-hour fire classification <p>Keystone openings accept Hubbell modular jacks, X-END connectors and flush multimedia Snap Fit connectors. Receptacles feature single or two circuit wiring and isolated ground capability.</p> | <p>Aluminum Finish Brass Finish Black/Brass Finish Black Gray</p> | <p>S1PT4X4AL S1PT4X4BRS S1PT4X4BRS3 S1PT4X4BL S1PT4X4GY</p> | <p>S1PT4X4ALJ S1PT4X4BRSJ S1PT4X4BRS3J S1PT4X4BLJ S1PT4X4GYJ</p> |
| <p>One-Piece Dual Style Line® Decorator Poke-Through Assembled-unit includes:</p> <ul style="list-style-type: none"> • Hubbell SystemOne dual channel floor fitting (S1PTFIT) • Dual Style Line® Decorator opening sub-plate (S1SP) • Finish flange and universal carpet cover assembly (S1CFCxx) • 4-hour fire classification <p>Style Line® Decorator openings accept two Style Line® Decorator or one surge or GFCI receptacle and one Style Line® Decorator receptacle. Outlet frames can be used to convert the application to a 6-port multi-service or a 12-port all communication solution. Fitting is 4-hr rated at 100% fill to accommodate (12) Cat 6A cables (0.330" diameter).</p> | <p>Aluminum Finish Brass Finish Black Gray</p> | <p>S1PTAL S1PTBRS S1PTBL S1PTGY</p> | <p>S1PTALJ S1PTBRSJ S1PTBLJ S1PTGYJ</p> |
| <p>One-Piece Modular AV Poke-Through Assembled-unit includes:</p> <ul style="list-style-type: none"> • Hubbell SystemOne AV floor fitting (S1PTAVFIT) • 20A, 125V power and 3-unit Hubbell iSTATION sub-plate (S1SP3IM) • Finish flange and universal carpet cover assembly (S1CFCxx) • 4-hour fire classification <p>The Hubbell iSTATION's recessed opening can accommodate datAVoice/audio and video solutions including 15-pin VGA, RCA, S-Video, 3.5mm stereo, X-END, HDMI and XLR microphone jacks.</p> | <p>Aluminum Finish Brass Finish Black Gray</p> | <p>S1PT3IMAL S1PT3IMBRS S1PT3IMBL S1PT3IMGY</p> | <p>S1PT3IMALJ S1PT3IMBRSJ S1PT3IMBLJ S1PT3IMGYJ</p> |
| <p>One-Piece Furniture Feed Poke-Through Assembled-unit includes:</p> <ul style="list-style-type: none"> • Hubbell SystemOne AV floor fitting (S1PTAVFIT) • Hubbell SystemOne Furniture Feed Cover Plate (S1SPFFxx) • 4-hour fire classification <p>This solution provides one ¾ in. conduit for power and one 1½ in. conduit for low-voltage. Furnished with two screw-in flexible metal conduit connectors.</p> | <p>Aluminum Finish Brass Finish Black Gray</p> | <p>S1PTFFAL S1PTFFBRS S1PTFFBL S1PTFFGY</p> | <p>S1PTFFALJ S1PTFFBRSJ S1PTFFBLJ S1PTFFGYJ</p> |



Note: *Junction box factory installed on through floor fitting.



Complies with UL514 A & C