

Encapsulated Cat #	Non-Encapsulated Cat #	Phase	Freq	CoilMat'l	kVA	Primary Voltage	Secondary Voltage	TempRise	Ambient Temp	Frame Size	Fuse Holder	Leads Out/Screw Terminals
9T58K0035	9T58R0035	1	50	CU	0.08	130/240	12/24	55	40	8100	NONE	Screw Terminals
9T58K0042	9T58R0042	1	60	CU	0.05	240x480	115	55	40	6100	NONE	Screw Terminals
9T58K0043	9T58R0043	1	60	CU	0.08	240x480	120	55	40	6125	NONE	Screw Terminals
9T58K0044	9T58R0044	1	60	CU	0.10	240x480	115	55	40	8100	NONE	Screw Terminals
9T58K0045	9T58R0045	1	60	CU	0.15	240x480	115	55	40	8150	NONE	Screw Terminals
9T58K0046	9T58R0046	1	60	CU	0.20	240x480	115	80	40	8175	NONE	Screw Terminals
9T58K0047	9T58R0047	1	60	CU	0.25	240x480	115	80	40	8200	NONE	Screw Terminals
9T58K0048	9T58R0048	1	60	CU	0.30	240x480	115	80	40	8250	NONE	Screw Terminals
9T58K0049	9T58R0049	1	60	CU	0.38	240x480	115	100	40	8250	NONE	Screw Terminals
9T58K0050	9T58R0050	1	60	CU	0.50	240x480	115	80	40	10225	NONE	Screw Terminals
9T58K0051	9T58R0051	1	60	CU	0.75	240x480	115	80	40	12225	NONE	Screw Terminals
9T58K0052	9T58R0052	1	60	CU	1.00	240x480	115	80	40	12300	NONE	Screw Terminals
9T58K0053	9T58R0053	1	60	CU	1.50	240x480	115	100	40	14225	NONE	Screw Terminals
9T58K0054	9T58R0054	1	60	CU	2.00	240x480	120	100	40	14300	NONE	Screw Terminals
9T58K0055	9T58R0055	1	60	CU	3.00	240x480	115	115	40	14475	NONE	Screw Terminals
9T58K0062	9T58R0062	1	50	CU	0.05	230/460/575	115/95	55	40	6150	NONE	Screw Terminals
9T58K0063	9T58R0063	1	50	CU	0.08	230/460/575	115/95	55	40	8100	NONE	Screw Terminals
9T58K0064	9T58R0064	1	50	CU	0.10	230/460/575	115/95	55	40	8150	NONE	Screw Terminals
9T58K0065	9T58R0065	1	50	CU	0.15	230/460/575	115/95	80	40	8200	NONE	Screw Terminals
9T58K0066	9T58R0066	1	50	CU	0.20	230/460/575	115/95	100	40	8200	NONE	Screw Terminals
9T58K0067	9T58R0067	1	50	CU	0.25	230/460/575	115/95	100	40	8250	NONE	Screw Terminals
9T58K0068	9T58R0068	1	50	CU	0.30	230/460/575	115/95	80	40	10225	NONE	Screw Terminals
9T58K0069	9T58R0069	1	50	CU	0.38	230/460/575	115/95	80	40	10225	NONE	Screw Terminals
9T58K0070	9T58R0070	1	50	CU	0.50	230/460/575	115/95	115	40	10225	NONE	Screw Terminals
9T58K0071	9T58R0071	1	50	CU	0.75	230/460/575	115/95	100	40	12300	NONE	Screw Terminals
9T58K0072	9T58R0072	1	50	CU	1.00	230/460/575	115/95	100	40	14225	NONE	Screw Terminals
9T58K0073	9T58R0073	1	50	CU	1.50	230/460/575	115/95	100	40	14300	NONE	Screw Terminals
9T58K0074	9T58R0074	1	50	CU	2.00	230/460/575	115/95	100	40	14475	NONE	Screw Terminals
9T58K0075	9T58R0075	1	60	CU	3.00	230x460	115	115	40	14475	NONE	Screw Terminals
9T58K0077	9T58R0077	1	60	CU	3.00	460/575	115	115	40	14475	NONE	Screw Terminals
9T58K0082	9T58R0082	1	50	CU	0.05	208/277/380	115/95	55	40	6150	NONE	Screw Terminals
9T58K0083	9T58R0083	1	50	CU	0.08	208/277/380	115/95	55	40	8100	NONE	Screw Terminals
9T58K0084	9T58R0084	1	50	CU	0.10	208/277/380	115/95	55	40	8150	NONE	Screw Terminals
9T58K0085	9T58R0085	1	50	CU	0.15	208/277/380	115/95	80	40	8200	NONE	Screw Terminals
9T58K0086	9T58R0086	1	50	CU	0.20	208/277/380	115/95	100	40	8200	NONE	Screw Terminals
9T58K0087	9T58R0087	1	50	CU	0.25	208/277/380	115/95	100	40	8250	NONE	Screw Terminals