

SINGLE-GANG DEVICE COVERS

Application

- For use whenever weatherproof protection is required for an outdoor receptacle


Product Features

- Rugged metallic construction
- State-of-the-art powder coat finish provides maximum weatherability and scratch resistance
- Self-closing lids assure weatherproof protection when the receptacle is not in use
- Includes installation hardware, gasket, and multi-lingual instructions

Compliances


-  US
- NEMA 3R Rated

GFCI STYLE COVERS




SINGLE RECEPTACLE STYLE COVERS


NOTE: DIMENSIONS FOR DEVICE-MOUNT AND BOX-MOUNT COVERS ARE THE SAME



DUPLEX STYLE COVER



CAT. NO. 5104-0, 5147-0



WEATHERPROOF BOXES, COVERS AND LIGHTING

ORDERING INFORMATION - DIMENSIONS

VERTICAL – DEVICE MOUNT					
CATALOG NUMBER	COLOR	RECEPTACLE TYPE	PKG. TYPE	STD. PKG.	UPC BAR CODE
5146-0	Gray	Duplex	Shrink	24	
5146-1	White	Duplex	Shrink	24	
5146-5	Gray	Duplex	Carded	6	
5147-0	Gray	Duplex	Shrink	24	
5103-0	Gray	GFCI	Shrink	24	
5103-1	White	GFCI	Shrink	24	
5103-2	Bronze	GFCI	Shrink	24	
5103-5	Gray	GFCI	Carded	6	
5103-6	White	GFCI	Carded	6	
5103-7	Bronze	GFCI	Carded	6	
5104-0	Gray	GFCI	Shrink	24	
5155-0	Gray	Single, 1.406" diameter	Shrink	24	
5155-1	White	Single, 1.406" diameter	Shrink	24	
5155-2	Bronze	Single, 1.406" diameter	Shrink	24	
5155-5	Gray	Single, 1.406" diameter	Carded	6	
5155-6	White	Single, 1.406" diameter	Carded	6	

VERTICAL – BOX MOUNT					
CATALOG NUMBER	COLOR	RECEPTACLE TYPE	PKG. TYPE	STD. PKG.	UPC BAR CODE
5095-0	Gray	Duplex	Shrink	24	
5091-0	Gray	Single, 1.406" diameter	Shrink	24	



C24

SINGLE-GANG BLANK COVERS AND MINI-PLATE

WEATHERPROOF BOXES, COVERS AND LIGHTING

Blank Covers Application

- For use whenever weatherproof protection is required for a single-gang box

Blank Covers Product Features

- Rugged metallic construction
- State-of-the-art powder coat finish provides maximum weatherability and scratch resistance

Blank Covers Compliances

-  UL
- NEMA 3R Rated

Mini-Plate Applications

- For use with light poles
- Provides a safe and convenient means of accessing power for holiday lighting, power tools, and the like

Mini-Plate Product Features

- Rugged metallic construction
- State-of-the-art powder coat finish provides maximum weatherability and scratch resistance
- Self-closing lid assures weatherproof protection when receptacle is not in use
- Includes installation hardware and receptacle



5173-0 TO 5173-7



5174-0



5183-0

ORDERING INFORMATION - DIMENSIONS

BLANK COVERS – DEVICE MOUNT

CATALOG NUMBER	COLOR	DESCRIPTION	PKG. TYPE	STD. PKG.	UPC BAR CODE
5173-0	Gray	Blank Cover	Shrink	50	
5173-1	White	Blank Cover	Shrink	50	
5173-5	Gray	Blank Cover	Carded	12	
5173-6	White	Blank Cover	Carded	12	
5173-7	Bronze	Blank Cover	Carded	12	

BLANK COVERS – BOX MOUNT


CATALOG NUMBER	COLOR	DESCRIPTION	PKG. TYPE	STD. PKG.	UPC BAR CODE
5174-0	Gray	Blank Cover	Shrink	50	

MINI-PLATE


CATALOG NUMBER	COLOR	DESCRIPTION	PKG. TYPE	STD. PKG.	UPC BAR CODE
5183-0	Black	Curved back, 1-1/2" radius - for 3" dia. pole mounting	Shrink	48	

Includes 125V, 15A 3-wire receptacle

BLANK COVERS



MINI-PLATE



TWO-GANG DEVICE COVERS



Application

- For use whenever weatherproof protection is required for an outdoor receptacle


Product Features

- Rugged metallic construction
- State-of-the-art powder coat finish provides maximum weatherability and scratch resistance
- Self-closing lids assure weatherproof protection when the receptacle is not in use
- Includes installation hardware, gasket, and multi-lingual instructions

Compliances


-  - Standard 514A (5132 - 5145)
-  - C22.2 (5132 - 5145)
- NEMA 3R Rated

5157-0, 5092-0




TWO-GANG DEVICE COVERS


5148-0 SERIES, 5096-0, 5160-0, 5098-0




5132-0




5133-0



5138-0



5145-0



NOTE: DIMENSIONS ARE THE SAME FOR DEVICE MOUNT AND BOX MOUNT STYLES SHOWN.
5157-0 SERIES, 5092-0



WEATHERPROOF BOXES,
COVERS AND LIGHTING

ORDERING INFORMATION - DIMENSIONS

DEVICE MOUNT					
CATALOG NUMBER	COLOR	RECEPTACLE TYPE	PKG. TYPE	STD. PKG.	UPC BAR CODE
5132-0	Gray	(2) Duplex	Shrink	10	
5138-0	Gray	(2) Round, 1.406" Dia.	Shrink	10	
5148-0	Gray	(2) Duplex	Shrink	18	
5148-5	Gray	(2) Duplex	Carded	4	
5157-0	Gray	(2) Single, 1.406" dia.	Shrink	18	
5160-0	Gray	(1) Duplex & (1) Single, 1.406" dia.	Shrink	12	

BOX MOUNT					
CATALOG NUMBER	COLOR	RECEPTACLE TYPE	PKG. TYPE	STD. PKG.	UPC BAR CODE
5096-0	Gray	(2) Duplex	Shrink	12	
5092-0	Gray	(2) Single, 1.406" dia.	Shrink	12	
5098-0	Gray	(1) Duplex & (1) Single, 1.406" dia.	Shrink	12	
5133-0	Gray	(1) Duplex, (1) GFCI	Shrink	10	
5145-0	Gray	(2) GFCI	Shrink	10	

C26

TWO AND THREE GANG DEVICE COVERS

WEATHERPROOF BOXES, COVERS AND LIGHTING

Applications

- For use whenever weatherproof protection is required for an outdoor receptacle
- Blank covers for use whenever weatherproof protection is required for a multi-gang box


Product Features

- Rugged metallic construction
- State-of-the-art powder coat finish provides maximum weatherability and scratch resistance
- Self-closing lids assure weatherproof protection when the receptacle is not in use
- Includes installation hardware, gasket, and multi-lingual instructions


Compliances

-  ^{WH}
- NEMA 3R Rated

THREE-GANG DEVICE COVERS 5097-0 AND 5093-0



BLANK COVERS 5177-0, 5175 SERIES



NOTE: DIMENSIONS ARE THE SAME FOR DEVICE MOUNT AND BOX MOUNT STYLES SHOWN.



ORDERING INFORMATION - DIMENSIONS

THREE-GANG DEVICE COVER – BOX MOUNT					
CATALOG NUMBER	COLOR	DESCRIPTION	PKG. TYPE	STD. PKG.	UPC BAR CODE
5097-0	Gray	(3) Duplex	Boxed	1	
5093-0	Gray	(3) Single, 1.406" dia.	Boxed	1	

THREE-GANG BLANK COVER – BOX MOUNT					
CATALOG NUMBER	COLOR	DESCRIPTION	PKG. TYPE	STD. PKG.	UPC BAR CODE
5177-0	Gray	Blank Cover	Boxed	10	

TWO-GANG BLANK COVER – DEVICE MOUNT					
CATALOG NUMBER	COLOR	DESCRIPTION	PKG. TYPE	STD. PKG.	UPC BAR CODE
5175-0	Gray	Blank Cover	Shrink	25	
5175-1	White	Blank Cover	Shrink	25	
5175-2	Bronze	Blank Cover	Shrink	25	
5175-5	Gray	Blank Cover	Carded	6	



SINGLE-GANG LEVER SWITCH COVERS

Application

- For use whenever weatherproof protection is required for an "on-off" type switch


Product Features

- Rugged metallic construction
- State-of-the-art powder coat finish provides maximum weatherability and scratch resistance
- Includes installation hardware and multi-lingual instructions.
- Single-gang covers are supplied with a switch — no need to purchase separate components
- Switch/cover units are supplied with the switch unassembled to the cover

Compliances

-  – Standard 514A
-  – Certified
- NEMA 3R Rated

SINGLE-GANG
5121 SERIES
5141 SERIES
CAT. NOS. 5128-0, 5137-0



5121-0 TO 5121-5
 5141-0 TO 5141-5
 5128-0, 5137-0

WEATHERPROOF BOXES,
COVERS AND LIGHTING

ORDERING INFORMATION - DIMENSIONS

SINGLE-GANG SWITCH COVERS – VERTICAL – DEVICE MOUNTED					
CATALOG NUMBER	COLOR	DESCRIPTION	PKG. TYPE	STD. PKG.	UPC BAR CODE
5121-0	Gray	SP 125V, 10A	Shrink	24	
5121-1	White	SP 125V, 10A	Shrink	24	
5121-2	Bronze	SP 125V, 10A	Shrink	24	
5121-5	Gray	SP 125V, 10A	Carded	6	
5141-0	Gray	3-Way 125V, 6A or 250V, 3A	Shrink	8	
5141-5	Gray	3-Way 125V, 6A or 250V, 3A	Carded	6	
5128-0	Gray	SP 120-277VAC, 20A	Shrink	20	
5137-0	Gray	DP 120-277VAC, 20A	Shrink	20	



C28

TWO-GANG LEVER SWITCH COVERS

WEATHERPROOF BOXES, COVERS AND LIGHTING

Application

- For use whenever weatherproof protection is required for an “on-off” type switch


Product Features

- Rugged metallic construction
- State-of-the-art powder coat finish provides maximum weatherability and scratch resistance
- Includes installation hardware and multi-lingual instructions.
- Most units supplied with a switch — no need to purchase separate components
- Switch/cover units are supplied with the switch unassembled to the cover


Compliances

-  – Standard 514A
-  – Certified
- NEMA 3R Rated

TWO-GANG CAT. NO. 5124-0, 5125 SERIES



TWO-GANG 5166 SERIES



5124-0

5166-0 TO 5166-5

5125-0


5167-0

ORDERING INFORMATION - DIMENSIONS

TWO-GANG SWITCH COVERS – DEVICE MOUNTED

CATALOG NUMBER	COLOR	DESCRIPTION	PKG. TYPE	STD. PKG.	UPC BAR CODE
5124-0	Gray	(2) SP 125V, 10A	Shrink	8	
5125-0	Gray	Cover only	Shrink	8	
5166-0	Gray	(1) SP 125V, 10A & (1) Duplex receptacle	Shrink	8	
5166-5	Gray	(1) SP 125V, 10A & (1) Duplex receptacle	Carded	4	
5167-0	Gray	2 Gang, Switch/GFCI Cover box mount	Shrink	8	

TWO-GANG 5167 SERIES



THREE-GANG LEVER SWITCH COVER & REPLACEMENT SWITCH

WEATHERPROOF BOXES, COVERS AND LIGHTING

Three-Gang Lever Switch Cover Application

- For use whenever weatherproof protection is required for an “on-off” type switch

Three-Gang Lever Switch Cover Product Features

- Rugged metallic construction
- State-of-the-art powder coat finish provides maximum weatherability and scratch resistance
- Includes installation hardware and multi-lingual instructions.
- Three-gang cover is supplied with switches — no need to purchase separate components
- Switch/cover units are supplied with the switch unassembled to the cover

Three-Gang Lever Switch Cover Compliances

-  UL
- NEMA 3R Rated (5126-0 only)



5126-0



5201-0

ORDERING INFORMATION - DIMENSIONS


THREE-GANG SWITCH COVER – DEVICE MOUNT

CATALOG NUMBER	COLOR	DESCRIPTION	PKG. TYPE	STD. PKG.	UPC BAR CODE
5126-0	Gray	(3) SP 125V, 10A	Boxed	1	


LEVER SWITCH COVER – ACCESSORIES

CATALOG NUMBER	COLOR	DESCRIPTION	PKG. TYPE	STD. PKG.	UPC BAR CODE
5201-0	—	SP 125V, 10A Toggle switch	Polybag	10	

THREE-GANG CATALOG NO. 5126-0



TOGGLE SWITCH CATALOG NOS. 5201-0



C30

CLUSTER COVERS

DIE CAST

WEATHERPROOF BOXES, COVERS AND LIGHTING

Applications

- For use with Bell® single-gang rectangular or round weather-proof boxes
- Cluster covers provide an easy means of mounting Bell® lampholders and other accessories


Product Features

- Rugged die cast construction
- State-of-the-art powder coat finish provides maximum weatherability and scratch-resistance
- Includes installation hardware, gasket, and multi-lingual instructions
- Three-hole covers are supplied with two closure plugs


Compliances

- – Standard 514A
- – Certified - C22.2 #18

RECTANGULAR CLUSTER COVERS 5186 SERIES, 5189 SERIES



ROUND CLUSTER COVERS 5193 SERIES, 5197 SERIES



5186-0 TO 5186-7



5193-0 TO 5193-7



5189-0 TO 5189-7



5197-0 TO 5197-7

ORDERING INFORMATION - DIMENSIONS

RECTANGULAR CLUSTER – COVERS

CATALOG NUMBER	COLOR	DESCRIPTION	PKG. TYPE	STD. PKG.	UPC BAR CODE
5186-0	Gray	1-1/2" Outlet	Shrink	20	
5186-1	White	1-1/2" Outlet	Shrink	20	
5186-2	Bronze	1-1/2" Outlet	Shrink	20	
5186-5	Gray	1-1/2" Outlet	Carded	6	
5186-6	White	1-1/2" Outlet	Carded	6	
5186-7	Bronze	1-1/2" Outlet	Carded	6	
5189-0	Gray	3-1/2" Outlets	Shrink	20	
5189-1	White	3-1/2" Outlets	Shrink	20	
5189-2	Bronze	3-1/2" Outlets	Shrink	20	
5189-5	Gray	3-1/2" Outlets	Carded	6	
5189-6	White	3-1/2" Outlets	Carded	6	
5189-7	Bronze	3-1/2" Outlets	Carded	6	

4" ROUND CLUSTER – COVERS

CATALOG NUMBER	COLOR	DESCRIPTION	PKG. TYPE	STD. PKG.	UPC BAR CODE
5193-0	Gray	1-1/2" Outlet	Shrink	20	
5193-1	White	1-1/2" Outlet	Shrink	20	
5193-2	Bronze	1-1/2" Outlet	Shrink	20	
5193-5	Gray	1-1/2" Outlet	Carded	6	
5193-6	White	1-1/2" Outlet	Carded	6	
5193-7	Bronze	1-1/2" Outlet	Carded	6	
5197-0	Gray	3-1/2" Outlets	Shrink	20	
5197-1	White	3-1/2" Outlets	Shrink	20	
5197-2	Bronze	3-1/2" Outlets	Shrink	20	
5197-5	Gray	3-1/2" Outlets	Carded	6	
5197-6	White	3-1/2" Outlets	Carded	6	
5197-7	Bronze	3-1/2" Outlets	Carded	6	

