



Wire Size	Model	SKU #	Lanyard Length	Weight per pc.	Ultimate Holding Value	No. of Crimps
8	<b>CR120</b>	617209994988	11"	0.04 lb.	200 lb.	One
8	<b>CR121</b>	617209994995	15"	0.04 lb.	200 lb.	One
8	<b>CR122</b>	617209995008	19"	0.04 lb.	200 lb.	One
8	<b>CR123</b>	617209995015	23"	0.04 lb.	200 lb.	One
6	<b>CR124</b>	617209995022	11"	0.06 lb.	300 lb.	One
6	<b>CR125</b>	617209995039	15"	0.06 lb.	300 lb.	One
6	<b>CR126</b>	617209995039	19"	0.06 lb.	300 lb.	One
6	<b>CR127</b>	617209995053	23"	0.06 lb.	300 lb.	One
4	<b>CR128</b>	617209995060	11"	0.06 lb.	350 lb.	One
4	<b>CR129</b>	617209995077	15"	0.06 lb.	350 lb.	One
4	<b>CR130</b>	617209995084	19"	0.06 lb.	350 lb.	One
4	<b>CR131</b>	617209995091	23"	0.06 lb.	350 lb.	One
3	<b>CR132</b>	617209995107	11"	0.07 lb.	500 lb.	One
3	<b>CR133</b>	617209995114	15"	0.07 lb.	500 lb.	One
3	<b>CR134</b>	617209995121	19"	0.07 lb.	500 lb.	One
3	<b>CR135</b>	617209995138	23"	0.07 lb.	500 lb.	One
2	<b>CR136</b>	617209995145	11"	0.07 lb.	600 lb.	One
2	<b>CR137</b>	617209995152	15"	0.07 lb.	600 lb.	One
2	<b>CR138</b>	617209995169	19"	0.07 lb.	600 lb.	One
2	<b>CR139</b>	617209995176	23"	0.07 lb.	600 lb.	One
1	<b>CR140</b>	617209995183	11"	0.10 lb.	1000 lb.	One
1	<b>CR141</b>	617209995190	15"	0.11 lb.	1000 lb.	One
1	<b>CR142</b>	617209995206	19"	0.11 lb.	1000 lb.	One
1	<b>CR143</b>	617209995213	23"	0.12 lb.	1000 lb.	One
1/O	<b>CR144</b>	617209995220	14"	0.11 lb.	1100 lb.	Two
1/O	<b>CR145</b>	617209995237	21"	0.13 lb.	1100 lb.	Two
1/O	<b>CR146</b>	617209995244	28"	0.14 lb.	1100 lb.	Two
1/O	<b>CR147</b>	617209995251	35"	0.15 lb.	1100 lb.	Two
2/O	<b>CR148</b>	617209995268	14"	0.22 lb.	1100 lb.	Two
2/O	<b>CR149</b>	617209995275	21"	0.25 lb.	1100 lb.	Two
2/O	<b>CR150</b>	617209995282	28"	0.28 lb.	1100 lb.	Two
2/O	<b>CR151</b>	617209995299	35"	0.31 lb.	1100 lb.	Two
3/O	<b>CR152</b>	617209995305	14"	0.25 lb.	1500 lb.	Two
3/O	<b>CR153</b>	617209995312	21"	0.27 lb.	1500 lb.	Two
3/O	<b>CR154</b>	617209995329	28"	0.30 lb.	1500 lb.	Two
3/O	<b>CR155</b>	617209995336	35"	0.32 lb.	1500 lb.	Two

Wire Size	Model	SKU #	Lanyard Length	Weight per pc.	Ultimate Holding Value	No. of Crimps
4/O	<b>CR156</b>	617209995343	14"	0.26 lb.	1700 lb.	Two
4/O	<b>CR157</b>	617209995350	21"	0.31 lb.	1700 lb.	Two
4/O	<b>CR158</b>	617209995367	28"	0.33 lb.	1700 lb.	Two
4/O	<b>CR159</b>	617209995374	35"	0.37 lb.	1700 lb.	Two
250	<b>CR160</b>	617209995381	14"	0.42 lb.	2000 lb.	Two
250	<b>CR161</b>	617209995398	21"	0.49 lb.	2000 lb.	Two
250	<b>CR162</b>	617209995404	28"	0.53 lb.	2000 lb.	Two
250	<b>CR163</b>	617209995411	35"	0.60 lb.	2000 lb.	Two
300	<b>CR164</b>	617209995428	14"	0.49 lb.	3000 lb.	Two
300	<b>CR165</b>	617209995435	21"	0.55 lb.	3000 lb.	Two
300	<b>CR166</b>	617209995442	28"	0.62 lb.	3000 lb.	Two
300	<b>CR167</b>	617209995459	35"	0.68 lb.	3000 lb.	Two
350	<b>CR168</b>	617209995466	14"	0.62 lb.	4000 lb.	Two
350	<b>CR169</b>	617209995473	21"	0.66 lb.	4000 lb.	Two
350	<b>CR170</b>	617209995480	28"	0.73 lb.	4000 lb.	Two
350	<b>CR171</b>	617209995497	35"	0.77 lb.	4000 lb.	Two
400	<b>CR172</b>	617209995503	14"	0.62 lb.	4500 lb.	Two
400	<b>CR173</b>	617209995510	21"	0.68 lb.	4500 lb.	Two
400	<b>CR174</b>	617209995527	28"	0.75 lb.	4500 lb.	Two
400	<b>CR175</b>	617209995534	35"	0.79 lb.	4500 lb.	Two
500	<b>CR176</b>	617209995541	14"	0.82 lb.	5000 lb.	Two
500	<b>CR177</b>	617209995558	21"	0.86 lb.	5000 lb.	Two
500	<b>CR178</b>	617209995565	28"	0.93 lb.	5000 lb.	Two
500	<b>CR179</b>	617209995572	35"	1.04 lb.	5000 lb.	Two
600	<b>CR180</b>	617209995589	14"	0.93 lb.	5500 lb.	Two
600	<b>CR181</b>	617209995596	21"	0.97 lb.	5500 lb.	Two
600	<b>CR182</b>	617209995602	28"	1.04 lb.	5500 lb.	Two
600	<b>CR183</b>	617209995619	35"	1.15 lb.	5500 lb.	Two
750	<b>CR184</b>	617209995626	14"	1.10 lb.	5500 lb.	Two
750	<b>CR185</b>	617209995633	21"	1.17 lb.	5500 lb.	Two
750	<b>CR186</b>	617209995640	28"	1.23 lb.	5500 lb.	Two
750	<b>CR187</b>	617209995657	35"	1.30 lb.	5500 lb.	Two
1000	<b>CR188</b>	617209995664	14"	1.21 lb.	5500 lb.	Two
1000	<b>CR189</b>	617209995671	21"	1.28 lb.	5500 lb.	Two
1000	<b>CR190</b>	617209995688	28"	1.35 lb.	5500 lb.	Two
1000	<b>CR191</b>	617209995695	35"	1.41 lb.	5500 lb.	Two

**Ask For Them By Name,  
iTOOLco's Window Crimp™ with Sure Grip**