

Grounding Accessories

- Solid and stranded pigtail lead wires are convenient for device grounding applications
- Grounding screws offer a unique thread-forming, hole-finding feature plus combination hex, Phillips, slotted and Robertson head

Grounding Tails - Stranded Wire




Fig. A - #14 AWG
Fig. B - #12 AWG



Fig. C




Fig. D




Fig. E

Stranded Wire Grounding Tails	Quantity	Cat. No.	Fig.
14 AWG stranded, 7-3/4 in. tail w/#10 fork & 10 ring and ground screw	Bag of 25	30-3183	A
12 AWG stranded, 7-3/4 in. tail w/#10 fork & 10 ring and ground screw	Bag of 25	30-3184	B
12 AWG stranded, 7-3/4 in. tail w/#10 fork & 10 ring and ground screw	Bundle of 100	30-3284	B
12 AWG solid tail, one stripped end, one end w/ground screw, joined to 12 AWG stranded tail at a ring terminal, w/fork terminal on second end	Bundle of 25	30-3286	—
12 AWG stranded, 2-wire tail joined w/#10 ring and ground screw, one stripped-end tail and one 10 fork tail	Bag of 25	30-3287	C
12 AWG stranded, 2-wire tail joined w/#10 ring and ground screw and two #10 fork tails	Bag of 25	30-3288	D
12 AWG stranded, 3-wire tail joined w/#10 ring and ground screw, one stripped-end tail and two 10 fork tails	Bag of 25	30-3289	E
12 AWG stranded, 7-3/4 in. tail w/#10 fork and #10 ring and ground screw	Plastic Box of 50	30-3385	B

Custom tails available. Contact your IDEAL Sales Representative for further information.

Grounding Tails - Solid Wire



Fig. A



Fig. A - 6-1/2 in. length

Fig. B - 7 in. length

Fig. C - 8 in. length

Fig. D - 10 in. length



Fig. E

Solid Wire Grounding Tails	Quantity	Cat. No.	Fig.
Pail-o-Tails™ 12 AWG solid, 6.5 in. tail w/loop & ground screw and stripped end	Pail of 500 (Bundles of 100)	30-3365	A
14 AWG solid, 8 in. tail w/loop & ground screw and stripped end	Box of 50	30-3390	E
12 AWG solid, 8 in. tail w/loop & ground screw and stripped end	Box of 50	30-3392	C
12 AWG solid, 10 in. tail w/loop & ground screw and stripped end	Bundle of 50	30-3394	D
12 AWG solid, 8 in. tail w/loop & ground screw and stripped end	Plastic box of 100	30-3399	C
12 AWG solid, 7 in. tail w/loop & ground screw and stripped end	Bag of 50	30-3407	B
12 AWG solid, 10 in. tail w/loop & ground screw and stripped end	Bag of 50	30-3410	D
12 AWG solid, 8 in. tail w/loop & ground screw and stripped end	Bundle of 50	30-3496	C

Grounding Accessories



Fig. A
Combo hex head
Thread-forming,
hole-finding
grounding screw

Fig. B

Grounding Accessories	Qty.	Cat. No.	Fig.
Ground Screw, thread-forming, hole-finding tip combination hex, Phillips, slotted and Robertson head	Pack of 50	30-3194	A
Ground Screw, thread-forming, hole-finding tip combination hex, Phillips, slotted and Robertson head	Bag of 100	30-3294	A
Grounding clip – accepts 10, 12 or 14 AWG Wire	Pack of 100	30-3395	B
Ground Screw, thread-forming, hole-finding tip combination hex, Phillips, slotted and Robertson head	Jar of 400	30-3494	A