




# TOOLS & SUPPLIES



Based on 2011 data available from Epicor/Vista.

## Conduit Benders

- Exceptional, durable, materials for extra strength
- Reinforced at stress points for longer life
- Markings are raised and cast into the bender body on both sides for easy visibility
- Deeply serrated step helps prevent slippage when applying force
- Grooved internal hook surface helps prevent conduit from slipping
- Flat hook surface provides stable starting point
- Desirable Benfield bending system



CONDUIT BENDERS

## Ductile Iron

- Withstands a lifetime of heavy use
- Ductile iron material is stronger than malleable iron or aluminum



### Ductile Iron Head & Handle Complete

| Conduit Type and Size                    | Cat. No. |
|--|----------|
| 1/2 in. EMT                              | 74-026   |
| 3/4 in. EMT, 1/2 in. Rigid & 1/2 in. IMC | 74-027   |
| 1 in. EMT, 3/4 in. Rigid & 3/4 in. IMC   | 74-028   |
| 1-1/4 in. EMT, 1 in. Rigid & 1 in. IMC   | 74-034   |

### Ductile Iron Head Only

| Conduit Type and Size                    | Cat. No. |
|--|----------|
| 1/2 in. EMT                              | 74-001   |
| 3/4 in. EMT, 1/2 in. Rigid & 1/2 in. IMC | 74-002   |
| 1 in. EMT, 3/4 in. Rigid & 3/4 in. IMC   | 74-003   |
| 1-1/4 in. EMT, 1 in. Rigid & 1 in. IMC   | 74-006   |

## Aluminum

- Lightweight aluminum for easy handling
- Strong enough for every day use



### Aluminum Head & Handle Complete

| Conduit Type and Size                    | Cat. No. |
|--|----------|
| 1/2 in. EMT                              | 74-046   |
| 3/4 in. EMT, 1/2 in. Rigid & 1/2 in. IMC | 74-047   |

### Aluminum Head Only

| Conduit Type and Size                    | Cat. No. |
|--|----------|
| 1/2 in. EMT                              | 74-031   |
| 3/4 in. EMT, 1/2 in. Rigid & 1/2 in. IMC | 74-032   |

## Handles For Benders

- Rugged, steel construction for long-term durability
- Baked-on blue enamel finish resists corrosion and enhances visibility
- Convenient bending guide for offset bends



### Handles for Ductile Iron

| Conduit Type and Size                    | Cat. No. |
|--|----------|
| 1/2 in. EMT                              | 74-019   |
| 3/4 in. EMT, 1/2 in. Rigid & 1/2 in. IMC | 74-019   |
| 1 in. EMT, 3/4 in. Rigid & 3/4 in. IMC   | 74-020   |
| 1-1/4 in. EMT, 1 in. Rigid & 1 in. IMC   | 74-021   |

### Handles for Aluminum

| Conduit Type and Size                    | Cat. No. |
|--|----------|
| 1/2 in. EMT                              | 74-019   |
| 3/4 in. EMT, 1/2 in. Rigid & 1/2 in. IMC | 74-019   |
| 1 in. EMT, 3/4 in. Rigid & 3/4 in. IMC   | 74-020   |
| 1-1/4 in. EMT, 1 in. Rigid & 1 in. IMC   | 74-021   |