

Compression F-Connector Port Seals



- For use with IDEAL RG-6, RG-6 Quad and RG-59 F-Style compression connectors to make connections water tight

Description	Qty.	Cat. No.
Port Seal	5	89-026

Push-on Connectors



- Permanent connection
- No termination tool needed

Description	Qty.	Cat. No.
RG-6 Push-on F-Connectors	4	85-065
RG-6Q Push-on F-Connectors	4	85-066
RG-59 Push-on F-Connectors	4	85-067
RG-6 Push-on F-Connectors	50	89-165
Coax Connector Kit w/Economy Coax Stripper & four RG-6 Push-On F-Connectors	—	33-320


F-Series Coaxial Connectors

F-Series Connectors utilize threaded couplings and cable conductors as contacts for CATV and other UHF applications.

Description	Quantity	Cat. No.
F-Series, Twist-on Plug, RG-59	Card of 4	84-018
	Card of 10	85-035
	Card of 4	84-016
F-Series, Crimp Plug, RG-59	Card of 10	85-036
	Card of 50	85-016
	Box of 100	86-016
	Card of 4	84-017
	Card of 10	85-037
F-Series, Crimp Plug, RG-6	Card of 50	85-017
	Box of 100	86-017
	Card of 4	84-030
	Card of 10	85-057
F-Series, Crimp Plug, RG-6, Quad Shield	Card of 50	85-030
	Box of 100	86-030
	Card of 10	85-031
F-Series, Female Adapter	Card of 10	85-031
F-Series, Terminator	Card of 10	85-038
F-Type, Twist-on RG-6	Card of 4	84-039
	Card of 10	85-053
	Card of 50	85-039
	Box of 100	86-039

Mini Compression Connectors

- For use with most 21-25 AWG mini coax cable
- Body is nickel plated for outstanding corrosion resistance
- Mini RCA head is gold plated for superior contact performance
- Bandwidth is 5 MHz - 3 GHz, Impedance is 75 Ohms (nominal), return loss min. -30 dB @ 3 GHz




F-Connector

RCA Connector

Description	Qty.	Cat. No.
Mini Compression F-Connector	10	89-014SM
Mini Compression RCA Connector	10	89-014SMRCA

Splitters



85-032

85-033

85-034

Description	Quantity	Cat. No.
CATV Cable Splitter, 5-900 MHz, 2-Way	Card of 1	85-032
	Box of 10	86-432
CATV Cable Splitter, 5-900 MHz, 3-Way	Card of 1	85-033
	Box of 10	86-433
CATV Cable Splitter, 5-900 MHz, 4-Way	Card of 1	85-034
High Performance Cable Splitter, 5MHz-1GHz 2-Way	Card of 1	85-132
	Box of 10	86-132
High Performance Cable Splitter, 5MHz-1GHz 3-Way	Card of 1	85-133
	Box of 10	86-133
High Performance Cable Splitter, 5MHz-1GHz 4-Way	Card of 1	85-134
	Box of 10	86-134

Satellite and Digital TV Splitters



85-332

85-333

85-334

- Designed for easy mounting over cable
- All ports are F female connectors, 75Ω
- Two grounding screws eliminate the need for grounding block
- Includes two mounting screws (Phillips/slotted head)

Description	Qty.	Cat. No.
2-Way, 5MHz - 2.3GHz	1	85-332
3-Way, 5MHz - 2.3GHz	1	85-333
4-Way, 5MHz - 2.3GHz	1	85-334