

## Compression F-Connector Port Seals



- For use with IDEAL RG-6, RG-6 Quad and RG-59 F-Style compression connectors to make connections water tight

Description	Qty.	Cat. No.
Port Seal	5	<b>89-026</b>

## Push-on Connectors



- Permanent connection
- No termination tool needed

Description	Qty.	Cat. No.
RG-6 Push-on F-Connectors	4	<b>85-065</b>
RG-6Q Push-on F-Connectors	4	<b>85-066</b>
RG-59 Push-on F-Connectors	4	<b>85-067</b>
RG-6 Push-on F-Connectors	50	<b>89-165</b>
Coax Connector Kit w/Economy Coax Stripper & four RG-6 Push-On F-Connectors	—	<b>33-320</b>

## F-Series Coaxial Connectors

F-Series Connectors utilize threaded couplings and cable conductors as contacts for CATV and other UHF applications.

Description	Quantity	Cat. No.
F-Series, Twist-on Plug, RG-59	Card of 4	<b>84-018</b>
	Card of 10	<b>85-035</b>
	Card of 4	<b>84-016</b>
F-Series, Crimp Plug, RG-59	Card of 10	<b>85-036</b>
	Card of 50	<b>85-016</b>
	Box of 100	<b>86-016</b>
	Card of 4	<b>84-017</b>
F-Series, Crimp Plug, RG-6	Card of 10	<b>85-037</b>
	Card of 50	<b>85-017</b>
	Box of 100	<b>86-017</b>
	Card of 4	<b>84-030</b>
F-Series, Crimp Plug, RG-6, Quad Shield	Card of 10	<b>85-057</b>
	Card of 50	<b>85-030</b>
	Box of 100	<b>86-030</b>
F-Series, Female Adapter	Card of 10	<b>85-031</b>
F-Series, Terminator	Card of 10	<b>85-038</b>
F-Type, Twist-on RG-6	Card of 4	<b>84-039</b>
	Card of 10	<b>85-053</b>
	Card of 50	<b>85-039</b>
	Box of 100	<b>86-039</b>

## Mini Compression Connectors

- For use with most 21-25 AWG mini coax cable
- Body is nickel plated for outstanding corrosion resistance
- Mini RCA head is gold plated for superior contact performance
- Bandwidth is 5 MHz - 3 GHz, Impedance is 75 Ohms (nominal), return loss min. -30 dB @ 3 GHz




F-Connector

RCA Connector

Description	Qty.	Cat. No.
Mini Compression F-Connector	10	<b>89-014SM</b>
Mini Compression RCA Connector	10	<b>89-014SMRCA</b>

## Splitters



85-032

85-033

85-034

Description	Quantity	Cat. No.
CATV Cable Splitter, 5-900 MHz, 2-Way	Card of 1	<b>85-032</b>
	Box of 10	<b>86-432</b>
CATV Cable Splitter, 5-900 MHz, 3-Way	Card of 1	<b>85-033</b>
	Box of 10	<b>86-433</b>
CATV Cable Splitter, 5-900 MHz, 4-Way	Card of 1	<b>85-034</b>
High Performance Cable Splitter, 5MHz-1GHz 2-Way	Card of 1	<b>85-132</b>
	Box of 10	<b>86-132</b>
High Performance Cable Splitter, 5MHz-1GHz 3-Way	Card of 1	<b>85-133</b>
	Box of 10	<b>86-133</b>
High Performance Cable Splitter, 5MHz-1GHz 4-Way	Card of 1	<b>85-134</b>
	Box of 10	<b>86-134</b>

## Satellite and Digital TV Splitters



85-332

85-333

85-334

- Designed for easy mounting over cable
- All ports are F female connectors, 75Ω
- Two grounding screws eliminate the need for grounding block
- Includes two mounting screws (Phillips/slotted head)

Description	Qty.	Cat. No.
2-Way, 5MHz - 2.3GHz	1	<b>85-332</b>
3-Way, 5MHz - 2.3GHz	1	<b>85-333</b>
4-Way, 5MHz - 2.3GHz	1	<b>85-334</b>