


### Wire-Nut® Wire Connector Sockets

- Speeds installation of Wire-Nut® Wire Connectors
- Fit any pneumatic or electric tool with a 1/4 in. chuck or drive socket



For Connector Model	Cat. No.
71B®, 71B® Black, 72B® & 72B® Black	<b>30-903</b>
73B® & 73B® Black	<b>30-904</b>
59B™	<b>30-905</b>
74B®, 76B® & 59B™	<b>30-906</b>

### Wire-Nut® Wire Connector Wrench

- Speeds installation of Wire-Nut® Wire Connectors
- Excellent leverage helps reduce fatigue



For Connector Model	Cat. No.
73B®, 74B® & 76B®	<b>H-632</b>

### Spin-Twist® Wire Connector Socket

- Speeds installation of IDEAL and BUCHANAN Wire Connectors
- For use with electric corded or cordless drill drivers
- 1/4 in. chuck fits most drills or drive sockets



For Connector Model	Cat. No.
Wire-Nut®, Wing-Nut®, Twister®, B-CAP® and WingTwist™	<b>30-902</b>

### Twist-a-Nut™ 7-in-1 Screwdriver


- Facilitate installation of connectors
- Universal Wire-Nut® Wrench in handle
- Accepts most twist-on connectors



Description	Cat. No.
7-in-1 Twist-a-Nut™	<b>35-908</b>

### Wire-Nut® Wire Connector Wrench/Screwdriver Combo


- Speeds installation of Wire-Nut® Wire Connectors
- Slotted-tip screwdriver with convenient connector-wrench socket in end of insulated handle



For Connector Model	Type	Cat. No.
74B® & 76B®	Mechanic – 1/4 in. x 4 in.	<b>30-331</b>
74B® & 76B®	Electrician – 3/16 in. x 6 in.	<b>30-333</b>

### Nutmaster® Nutdrivers

- Speeds installation of Twister® Wire Connectors
- Nickel/chrome plated to resist rust and corrosion
- Cushioned rubber grip



For Connector Model	Cat. No.
341®	<b>35-292</b>
342®	<b>35-295</b>

### Ratch Wrench

- Speeds installation of B-CAP® Wire Connectors
- Either end accepts 1/4-in. drive for tight-spot wire splicing



For Connector Model	Cat. No.
B1, B2 & B4	<b>BR-5</b>

### High-Speed Wire Connector Chuck

- Cordless screwdriver adapter for installing B-CAP® Wire Connectors




For Connector Model	Cat. No.
B1, B2 & B4	<b>HSC-1</b>

## Nutmaster® Nutdrivers




- Long, hollow shank handles longer bolts
- Identification and color coding on ends
- Nickel/chrome plated to resist rust and corrosion
- Cushioned rubber grips
- Models 35-292 and 35-295 fit Twister® Wire Connectors



Description	Shaft Length	Color	Cat. No.
3/16 in.	3-1/4 in.	Black	<b>35-290</b>
1/4 in.	3-1/4 in.	Red	<b>35-291</b>
5/16 in.	3-1/4 in.	Yellow	<b>35-292</b>
11/32 in.	3-1/4 in.	Green	<b>35-293</b>
3/8 in.	3-1/4 in.	Blue	<b>35-294</b>
7/16 in.	4 in.	Brown	<b>35-295</b>
1/2 in.	4 in.	Red	<b>35-296</b>

## Slim Electronics



- Designed for maximum handling comfort when working in tight areas
- Tough, chrome vanadium steel shank
- Phosphate tip for longer wear life
- Rotating cap for optimum control for precise centering
- Color-coded cap for easy identification



Description	Style	Blade Length	Cat. No.
3/32 in.	Cabinet Tip	2-1/2 in.	<b>36-240</b>
3/32 in.	Cabinet Tip	3 in.	<b>36-241</b>
1/8 in.	Cabinet Tip	4 in.	<b>36-242</b>
1/8 in.	Cabinet Tip	6 in.	<b>36-243</b>
5/32 in.	Cabinet Tip	4 in.	<b>36-244</b>
5/32 in.	Cabinet Tip	6 in.	<b>36-245</b>
#0 - 1/8 in.	Phillips head	2-1/2 in.	<b>36-246</b>
7-Piece Set includes one each of 36-240 thru 36-246			<b>36-248</b>
4-Piece Set includes one each of 36-240, -241, -242 & -246			<b>36-249</b>

## 7-Piece Nutdriver Set

### Includes:

- 3/16 in. x 3-1/4 in.
- 1/4 in. x 3-1/4 in.
- 5/16 in. x 3-1/4 in.
- 11/32 in. x 3-1/4 in.
- 3/8 in. x 3-1/4 in.
- 7/16 in. x 4 in.
- 1/2 in. x 4 in.



Description	Cat. No.
7-Piece Nutdriver Set	<b>35-299</b>

## 10-in-1 Screwdriver/Nutdriver

- Includes 1/4 in. slotted, #2 Phillips, 3/16 in. slotted, #1 Phillips, #1 & #2 square recess, #15 and #10 Torx® and 5/16 in. & 1/4 in. Nutdriver
- Cushion grip for comfort and performance



Description	Cat. No.
10-in-1 Screwdriver/Nutdriver	<b>35-910</b>

### Replacement Bits (for 10-in-1 Screwdriver)

Description	Cat. No.
1/4 in. slotted - #2 Phillips (2/pack)	<b>35-940</b>
3/16 in. slotted - #1 Phillips (2/pack)	<b>35-941</b>
#1 & #2 Square Recess (2/pack)	<b>35-942</b>
#15 & #10 Torx® (2/pack)	<b>35-943</b>

*Torx® is a trademark of Camcar division of Textron, Inc.*

## 5-in-1 Screwdriver/Nutdriver

- Contains: 5/16 in. nutdriver, #1 Phillips, #2 Phillips, 9/32 in. slotted and 3/16 in. slotted
- Cushion grip for performance and comfort



Description	Cat. No.
5-in-1 Screwdriver/Nutdriver	<b>35-905</b>

### Replacement Bits (for 5-in-1 Screwdriver)

Description	Cat. No.
#1 Phillips - 3/16 in. slotted	<b>LA-4123</b>
#2 Phillips - 9/32 in. slotted	<b>LA-4124</b>