

Vol-Con® Voltage/Continuity Tester



- Multi-function solenoid device operates as three testers in one
- Heavy-duty voltage tester tests up to 600VAC/DC
- Low-voltage indicator tests as low as 5VAC/DC
- Patented, automatic switching continuity tester protects against contact with live voltage
- Built-in safety check for testing leads
- LED and neon indicator lamps
- Replaceable plug-in leads for quick and easy changes
- Flexible 30 in., oil-resistant vinyl leads with right-angle plug for strain relief
- Rugged, high-impact case with ultrasonically welded seams protect against dust and moisture



Batteries included. Convenient, snap-out battery replacement.

Description	Cat. No.	Replacement Leads Cat. No.
Vol-Con® w/standard leads	61-076	61-070
Vol-Con® w/slim-line leads	61-079	61-078
Vol-Con® w/resistor-fused leads*	61-080	61-072
Vinyl case	61-009	—
Standard leather case	61-010	—
Premium leather case	61-020	—
Replacement battery set**	61-201	—

*Special current-limiting resistors in each lead act as fuses in case of accidental shorts or breakdowns and limit current in leads to prevent dangerous arcing.

**Four 1-1/2V batteries. Tester will also accept Union Carbide A76 or Eveready No. 357 batteries.



Vol-Con® Lite Voltage/Continuity Testers



Vol-Con® Voltage/Continuity Tester features plus:

- Dual voltage indicators to identify AC/DC ranges from 5V to 480VAC and 120V to 240VDC
- Slim-line design for easy handling and convenient pocket storage
- Top-mounted lead plug assembly for reduced cord tangling
- Audible voltage and continuity detection (61-101 and 61-102)
- Rugged, high-impact case with ultrasonically welded seams to protect against dust and moisture



Batteries included. Convenient, snap-out battery replacement.

Description	Cat. No.	Replacement Leads Cat. No.
Vol-Con® Lite w/slim-line leads	61-099	61-081
Vol-Con® Lite w/resistor-fused leads*	61-100	61-082
Vol-Con® Lite Audible w/slim-line leads	61-101	61-081
Vol-Con® Lite Audible w/resistor-fused leads*	61-102	61-082
Insulated clip lead set (1 prod & 1 alligator clip)	61-083	—
Premium leather case	61-029	—
Standard leather case	61-012	—
Replacement battery set**	61-201	—

*Special current-limiting resistors in each lead act as fuses in case of accidental shorts or breakdowns and limit current in leads to prevent dangerous arcing.

**Four 1-1/2V batteries. Tester will also accept Union Carbide A76 or Eveready No. 357 batteries.

