

# CUTTING




**MMT410**  
3-1/8" Titanium STORM  
Titanium HSS  
Metal, Wood, Fiberglass



**MM400**  
3-1/8" Full Round  
HSS  
Metal, Wood, Fiberglass



**MM410**  
3-1/8" Segment  
HSS  
Metal, Wood, Fiberglass



**MM450**  
4" Circular  
HSS  
Hardwood, Laminate



**MM415**  
1-3/8" Deep Plunge  
HSS  
Metal, Wood, Fiberglass



**MM390**  
90° REACH  
Bi-Metal  
Hardwood, Laminate,  
Parquet



**MMV**  
MM150, MM200, MM300  
HCS & Bi-Metal  
Wood, Drywall, PVC, Metal



**MM550**  
2-1/2" Wavy Knife Blade  
HCS  
Rubber, Insulation

# ADAPTERS

Adapt the Rockwell® Sonicrafter, Porter-Cable® Multi-Tool, or Fein SuperCut to fit any Imperial Blades accessories



**ADRW**  
Rockwell® Sonicrafter  
Adapter



**ADPC**  
Porter-Cable® Multi-Tool  
Adapter KIT



**ADSC**  
Fein SuperCut  
Adapter

# GRINDING & SCRAPING



**MM610**  
2-1/2" Segmented  
Carbide  
Grout, Plaster



**MM620**  
Triangle RASP  
Carbide  
Mortar, Thinset



**MM625**  
Finger RASP  
Carbide  
Mortar, Thinset



**MM630**  
Segment  
Carbide  
Grout, Drywall



**MM640**  
1-1/4" Flush Cut  
Carbide  
Grout, Plaster, Drywall



**MM710**  
2-1/2" Segmented  
Diamond  
Grout, Plaster



**MM730**  
Segment  
Diamond  
Grout, Plaster



**MM740**  
1-1/4" Flush Cut  
Diamond  
Grout, Plaster



**MM500**  
Rigid Scraper  
Stainless Steel  
Adhesive, Caulk, Paint



**MM510**  
Flexible Scraper  
Spring Steel  
Caulk, Glue, Putty



**MM520**  
Flexible Scraper with  
Knife Edge  
Stainless Steel  
Caulk, Paint



**MM530**  
Segmented Knife Blade  
Stainless Steel  
Window Putty



**MM541**  
1-3/8" Sealant Cutter  
Stainless Steel  
Sealant, Caulk



**MM560**  
Tapered Sealant Cutter  
Stainless Steel  
Sealant, Caulk

# SANDING



**TSP**  
Triangle Sanding Pad



**RSP**  
4-1/2" Round Sanding Pad



**SP60**  
60 Grit Sandpaper  
5 and 50 packs



**SP80**  
80 Grit Sandpaper  
5 and 50 packs



**SP120**  
120 Grit Sandpaper  
5 and 50 packs



**SP180**  
180 Grit Sandpaper  
5 and 50 packs














**SP220**  
220 Grit Sandpaper  
5 and 50 packs




**SPV**  
Variety Grit - 50 Pack  
60, 80, 120, 180, and 220  
grit sandpapers

# APPLICATION


											
<b>TITANIUM ENHANCED</b>	•	•	•	•	•	•	•				
<b>BI-METAL</b>	•	•	•	•	•	•	•				
<b>HCS</b>					•	•	•				
<b>CARBIDE</b>								•	•		
<b>DIAMOND</b>								•	•		
<b>SPECIALTY</b>			•							•	•

# UNIVERSAL FIT


  
**Fein**  
 Multimaster FMM250,  
 FMM250Q, MSXE 636





  
**Makita**  
 Multi-Tool  
 TM3000CX5





  
**Bosch**  
 Multi-X  
 MX30EC, PS50



  
**Dremel**  
 Multi-Max 6300,  
 6300, MM20, MM40



  
**Rockwell**  
 SoniCrafter  
 RK5100K, RK2514K2



  
**Milwaukee**  
 Multi-Tool  
 2426



**MADE IN THE USA**

Contact your local dealer