

# ILSCO Insulated Service Entrance Sleeves

A



## TYPE P840

### Features

- Pre-insulated
- Concave polyethylene end caps
- Dual rated
- Meets ANSI C119.4 requirements
- RUS Listed
- Die Index 840

### Benefits

- Fast, easy installation
- Seal out dirt but are easily pierced when inserting conductor
- For use with aluminum-aluminum and aluminum-copper conductors
- Ensures reliability



Catalog Number	End "A"					End "B"					Color Code
	Conductor Range		Diameter		Color Code	Conductor Range		Diameter			
	ACSR	AWG	max.	min.		ACSR	AWG	max.	min.		
PICS-834	1/0	2/0 (compact) or 1/0	0.398	0.365	Yellow	4	2 sol - 3-4 str	0.258	0.213	Orange	
PICS-835	1/0	2/0 (compact) or 1/0	0.398	0.365	Yellow	2	1-2 str	0.328	0.268	Red	
PICS-836	1/0	2/0 (compact) or 1/0	0.398	0.365	Yellow	1/0	2/0 (compact) or 1/0	0.398	0.365	Yellow	
PICS-844	2/0	3/0 (compact) or 2/0	0.448	0.414	Gray	4	2 sol - 3-4 str	0.258	0.213	Orange	
PICS-845	2/0	3/0 (compact) or 2/0	0.448	0.414	Gray	2	1-2 str	0.328	0.268	Red	
PICS-846	2/0	3/0 (compact) or 2/0	0.448	0.414	Gray	1/0	2/0 (compact) or 1/0	0.398	0.365	Yellow	
PICS-847	2/0	3/0 (compact) or 2/0	0.448	0.414	Gray	2/0	3/0 (compact) or 2/0	0.448	0.414	Gray	
PICS-854	3/0	4/0 (compact) or 3/0	0.502	0.464	Black	4	2 sol - 3-4 str	0.258	0.213	Orange	
PICS-855	3/0	4/0 (compact) or 3/0	0.502	0.464	Black	2	1-2 str	0.328	0.268	Red	
PICS-856	3/0	4/0 (compact) or 3/0	0.502	0.464	Black	1/0	2/0 (compact) or 1/0	0.398	0.365	Yellow	
PICS-857	3/0	4/0 (compact) or 3/0	0.502	0.464	Black	2/0	3/0 (compact) or 2/0	0.448	0.414	Gray	
PICS-858	3/0	4/0 (compact) or 3/0	0.502	0.464	Black	3/0	4/0 (compact) or 3/0	0.502	0.464	Black	
PICS-864	4/0	4/0	0.564	0.522	Pink	4	2 sol - 3-4 str	0.258	0.213	Orange	
PICS-865	4/0	4/0	0.564	0.522	Pink	2	1-2 str	0.328	0.268	Red	
PICS-866	4/0	4/0	0.564	0.522	Pink	1/0	1/0	0.398	0.365	Yellow	
PICS-867	4/0	4/0	0.564	0.522	Pink	2/0	3/0 (compact) or 2/0	0.448	0.414	Gray	
PICS-868	4/0	4/0	0.564	0.522	Pink	3/0	4/0 (compact) or 3/0	0.502	0.464	Black	
PICS-869	4/0	4/0	0.564	0.522	Pink	4/0	4/0	0.564	0.522	Pink	



4730 Madison Road, Cincinnati, Ohio 45227-1426 Phone 513 533-6200 Fax 513 871-4084 Web site www.ilsco.com  
 Canada 1050 Lakeshore Road East, Mississauga, Ontario, Canada L5E1E4 Phone 905 274-2341 Fax 905 274-8763