

## Kwikon ENT - Blue Stripe



|      | Size (in) | Length (ft) | Product Code | Weight lbs/pkg |
|------|-----------|-------------|--------------|----------------|
| Reel | 1/2       | 1500        | 012002       | 165            |
|      | 3/4       | 1000        | 012011       | 158            |
|      | 1         | 750         | 012021       | 160            |
|      | 1-1/4     | 1000        | 012047       | 193            |
|      | 1-1/2     | 750         | 012033       | 205            |
|      | 2         | 500         | 012044       | 220            |
| Coil | 1/2       | 200         | 012031       | 20             |
|      | 3/4       | 100         | 012040       | 12.5           |
|      | 1         | 100         | 012041       | 17             |
|      | 1-1/4     | 500         | 012046       | 76             |
|      | 1-1/2     | 300         | 012032       | 50.5           |
|      | 2         | 225         | 012043       | 69.5           |

Wrapped in plastic, coils are easily dispensed from the center.

## Kwikon ENT Reels - Color Coded

| Size (in) | Length (ft) | Product Code |        |        | Weight lbs/reel |
|-----------|-------------|--------------|--------|--------|-----------------|
|           |             | Red          | Yellow | Blue   |                 |
| 1/2       | 1500        | 012305       | 012335 | 012002 | 165             |
| 3/4       | 1000        | 012307       | 012337 | 012011 | 158             |
| 1         | 750         | 012310       | 012340 | 012021 | 160             |
| 1-1/4     | 1000        | 012037       | 012038 | 012047 | 193             |
| 1-1/2     | 750         | 012035       | 012036 | 012033 | 205             |
| 2         | 500         | 012039       | 012042 | 012044 | 220             |

## Kwikon ENT - 10' Sticks with Blue Stripe

| Size (in) | Length (ft) | Product Code | Crate Qty |
|-----------|-------------|--------------|-----------|
| 1/2       | 10          | 012001       | 3,600     |
| 3/4       | 10          | 012010       | 2,200     |
| 1         | 10          | 012034       | 1,800     |

All Kwikon ENT is UL Listed for use in walls, floor slabs and ceilings, as outlined in Article 362 of the 2005 NEC Code.

## Storage of Kwikon ENT Tubing

Manufacturer recommends that ENT tubing should not be stored outdoors where subjected to direct sunlight without protective covering, i.e. packaging or tarps.



E 122659



TC-13

## Kwikon Coupling



| Size (in) | Part Number | Product Code |
|-----------|-------------|--------------|
| 1/2       | KC10        | 089000       |
| 3/4       | KC15        | 089001       |
| 1         | KC20        | 089002       |
| 1-1/4     | KC25        | 189670       |
| 1-1/2     | KC30        | 189671       |
| 2         | KC35        | 189672       |

## Kwikon Connector For Concrete Encasement



| Size (in) | Part Number | Product Code |
|-----------|-------------|--------------|
| 1/2       | KTA10       | 089006       |
| 3/4       | KTA15       | 089007       |
| 1         | KTA20       | 089008       |
| 1-1/4     | KTA25       | 189680       |
| 1-1/2     | KTA30       | 189681       |
| 2         | KTA35       | 189682       |

## Kwikon Snap-in Connector



| Size (in) | Part Number | Product Code |
|-----------|-------------|--------------|
| 1/2       | KTS10       | 089146       |
| 3/4       | KTS15       | 089147       |
| 1         | KTS20       | 089148       |

## Kwikon Transition Coupling



| Size (in) | Part Number | Product Code |
|-----------|-------------|--------------|
| 1/2       | KTC10       | 089012       |
| 3/4       | KTC15       | 089013       |
| 1         | KTC20       | 089014       |



E 59258, E 119384



TC-13



C22.2 No. 227.1

