



PROJECT:
TYPE:
ORDERING # :
COMMENTS:

## TRANSFORMER ACCESSORIES

TRANSFORMER ACCESSORIES	TRANSFORMER ACCESSORIES	ADDITIONAL ACCESSORIES	ADDITIONAL ACCESSORIES
<p><b>15557BK</b> - Mechanical Transformer Timer</p> <ul style="list-style-type: none"> <li>- Dimensions: 3" W x 3.09" H x 2.75" L</li> <li>- Plug-In Timer For Use With All Professional Series Transformers</li> <li>- Suitable For All Professional Series Transformers</li> </ul> 	<p><b>15565BK</b> - Plug-In Transformer Photocell</p> <ul style="list-style-type: none"> <li>- Plug-In Photocell</li> </ul> 	<p><b>Low Voltage Cable</b> - UL Listed For 12V Outdoor Lighting Applications. UV Stabilized PVC Insulation. For Direct Burial</p> <ul style="list-style-type: none"> <li><b>15501BK</b> - 12-Gauge 100' Cable</li> <li><b>15502BK</b> - 12-Gauge 250' Cable</li> <li><b>15505BK</b> - 8-Gauge 250' Cable</li> <li><b>15506BK</b> - 10-Gauge 250' Cable</li> <li><b>15504BK</b> - 12-Gauge 500' Cable</li> <li><b>15503BK</b> - 12-Gauge 1000' Cable</li> </ul> 	<p><b>QUIC DISC Connector</b> - Joins #18-2 Fixture Leads With #12-2 or #10-2 Low Voltage Cable. Injection-Molded Polycarbonate With Nickel-Plated Brass Contacts For Maximum Corrosion Protection &amp; Improved Conductivity</p> <p><b>15509BK</b> - Use Only With #12-2 or #10-2 Cable</p> 
<p><b>15556WH</b> - Digital Transformer Timer</p> <ul style="list-style-type: none"> <li>- Dimensions: 2.73" W x 3.84" H x 1.89" L</li> <li>- Plug-In Digital Timer For Use With All Professional Series Transformers</li> <li>- Battery Backup Included</li> <li>- Straightforward Programming &amp; Easy Daylight Savings Changeover</li> <li>- Suitable For All Professional Series Transformers</li> </ul> 	<p><b>15511BK</b> - Synchronizer Device</p> <ul style="list-style-type: none"> <li>- Synchronize All Transformers Used in a Landscape Setting so They Turn on &amp; Off at The Same Time (Jumper Wire is Not Included)</li> </ul> 	<p><b>Gel-Filled Wire Connector</b> - Offers Twist-On Waterproof, In-Line Cable Splicing For Direct Burial. Services 12V &amp; 120V Line Voltage</p> <p><b>15579BK</b> - For Use When Connecting:</p> <ul style="list-style-type: none"> <li>- 8-Gauge Wire to 10-Gauge &amp; 12-Gauge Wire</li> <li>- 10-Gauge to 12-Gauge Wire</li> </ul> <p><b>15589BK</b> - For Use When Connecting:</p> <ul style="list-style-type: none"> <li>- 10-Gauge Wire - 12-Gauge Wire</li> <li>- 10-Gauge Wire to 12-Gauge Wire</li> <li>- 12-Gauge Wire to 18-Gauge Wire</li> </ul> 	<p><b>Pro Series Wire Connector</b> - Gel-Filled Wire Connector Provides a Watertight, Long Lasting Connection. Suitable For Direct Burial. Connects Two #12 Gauge to One #18 Gauge. Two Connectors Required Per Connection</p> <p><b>15529BK</b> - Bulk Pack of 100 Connectors, Packed in Sealed Bags of 10</p> 
<p><b>15534BK</b> - Remote Plug-In Transformer Photocell</p> <ul style="list-style-type: none"> <li>- Plug-In Photocell With 10' Cord</li> </ul> 			

## NOTES

We reserve the right to revise the design or components of any product due to parts availability or change in UL standards, without assuming any obligation or liability to modify any products previously manufactured, and without notice.

