

Journeyman™ Screwdriver Sets

5-Piece Journeyman™ Screwdriver Set

Additional Features:

- General purpose selection of the most frequently used screwdrivers.

Cat. No.	Set Contains	Weight (lbs.)	
JSDS01		1.15	
Cat. No.	Description	Shaft Length	Overall Length
JSD6C06	3/16" cabinet-tip	6" (152 mm)	10-1/4" (260 mm)
JSD4K08	1/4" keystone-tip	4" (102 mm)	9" (228 mm)
JSD6K09	5/16" keystone-tip	6" (152 mm)	11" (279 mm)
JSD4PH1	#1 Phillips-tip	4" (102 mm)	8-1/4" (210 mm)
JSD4PH2	#2 Phillips-tip	4" (102 mm)	9" (228 mm)

JOURNEYMAN



JSDS01


7-Piece Journeyman™ Screwdriver Set

Additional Features:

- Accommodates a broad range of standard fastener sizes.

Cat. No.	Set Contains	Weight (lbs.)	
JSDS02		1.65	
Cat. No.	Description	Shaft Length	Overall Length
JSD4C06	3/16" cabinet-tip	4" (102 mm)	8-1/4" (210 mm)
JSD6C06	3/16" cabinet-tip	6" (152 mm)	10-1/4" (260 mm)
JSD4K08	1/4" keystone-tip	4" (102 mm)	9" (228 mm)
JSD6K09	5/16" keystone-tip	6" (152 mm)	11" (279 mm)
JSD4PH1	#1 Phillips-tip	4" (102 mm)	8-1/4" (210 mm)
JSD4PH2	#1 Phillips-tip	4" (102 mm)	9" (228 mm)
JSD6PH3	#2 Phillips-tip	6" (152 mm)	11" (279 mm)

JOURNEYMAN



JSDS02

Journeyman™ Screwdrivers

Journeyman™ Cabinet-Tip Screwdrivers – Round Shaft

Additional Features:

- Narrow cabinet-tip permits blade access where space is limited.
- Exceptionally hard steel shaft efficiently transfers torque into the tip.

Cat. No.	Shaft Tip Width	Shaft Length	Overall Length	Weight (lbs.)
JSD4C06	3/16" (5 mm)	4" (102 mm)	8-1/4" (210 mm)	0.15
JSD6C06	3/16" (5 mm)	6" (152 mm)	10-1/4" (260 mm)	0.15

JOURNEYMAN



JSD6C06

All dimensions are in inches and (millimeters).

⚠ WARNING: NOT insulated. Will NOT protect against electrical shock.

