

### Group EE

VA	Catalog Number	Fig	Dimensions*					Est. Ship Weight	Temp Rise	Insulation Temp.	Secondary Fuse Clip	Terminal Cover	Fuse Block
			A	B	C	D	E						
<b>550/575/600 - 110/115/120</b>													
50	631-1104-000	14	3.78	3.00	2.73	1.96	2.50	2.8	55	105	Included	631-0000-004	631-0000-001
75	631-1204-000	14	4.03	3.00	2.73	2.42	2.50	3.5	55	105	Included	631-0000-004	631-0000-001
100	631-1304-000	14	4.03	3.38	3.04	2.42	2.81	4.3	55	105	Included	631-0000-004	631-0000-001
150	631-1404-000	14	4.03	3.75	3.35	2.82	3.13	5.6	80	130	Included	631-0000-004	631-0000-001
200	631-1504-000	14	4.37	4.50	3.98	2.62	3.75	7.7	80	130	Included	631-0000-004	631-0000-001
250	631-1604-000	14	4.37	4.50	3.98	2.82	3.75	8.3	80	130	Included	631-0000-004	631-0000-001
300	631-1704-000	14	4.74	4.50	3.98	3.19	3.75	9.7	80	130	Included	631-0000-004	631-0000-001
350	631-1804-000	14	4.74	4.50	3.98	3.74	3.75	10.4	80	130	Included	631-0000-004	631-0000-001
500	631-1904-000	14	6.11	5.25	4.64	3.87	4.38	14.5	80	130	Included	631-0000-006	631-0000-001
750	631-2004-000	14	7.61	5.25	4.64	5.37	4.38	27.6	80	130	Included	631-0000-006	631-0000-001

### Group FF

VA	Catalog Number	Fig	Dimensions*					Est. Ship Weight	Temp Rise	Insulation Temp.	Secondary Fuse Clip	Terminal Cover	Fuse Block
			A	B	C	D	E						
<b>208 x 277 - 120</b>													
50	631-1105-000	14	3.78	3.00	2.73	1.96	2.50	2.8	55	105	Included	631-0000-004	631-0000-001
75	631-1205-000	14	4.03	3.00	2.73	2.42	2.50	3.5	55	105	Included	631-0000-004	631-0000-001
100	631-1305-000	14	4.03	3.38	3.04	2.42	2.81	4.3	55	105	Included	631-0000-004	631-0000-001
150	631-1405-000	14	4.03	3.75	3.35	2.82	3.13	5.6	80	130	Included	631-0000-004	631-0000-001
200	631-1505-000	14	4.37	4.50	3.98	2.62	3.75	7.7	80	130	Included	631-0000-004	631-0000-001
250	631-1605-000	14	4.37	4.50	3.98	2.82	3.75	8.3	80	130	Included	631-0000-004	631-0000-001
300	631-1705-000	14	4.74	4.50	3.98	3.19	3.75	9.7	80	130	Included	631-0000-004	631-0000-001
350	631-1805-000	14	4.74	4.50	3.98	3.74	3.75	10.4	80	130	Included	631-0000-004	631-0000-001
500	631-1905-000	14	6.11	5.25	4.64	3.87	4.38	14.5	80	130	Included	631-0000-006	631-0000-001
750	631-2005-000	14	7.61	5.25	4.64	5.37	4.38	27.6	80	130	Included	631-0000-006	631-0000-001

### Group GG

VA	Catalog Number	Fig	Dimensions*					Est. Ship Weight	Temp Rise	Insulation Temp.	Secondary Fuse Clip	Terminal Cover	Fuse Block
			A	B	C	D	E						
<b>208 x 230 x 460 - 115</b>													
50	631-1106-000	14	3.77	3.00	2.73	2.21	2.50	2.8	55	105	Included	631-0000-004	631-0000-001
75	631-1206-000	14	4.02	3.38	3.04	2.42	2.81	3.5	55	105	Included	631-0000-004	631-0000-001
100	631-1306-000	14	4.02	3.38	3.04	2.62	2.81	4.3	55	105	Included	631-0000-004	631-0000-001
150	631-1406-000	14	4.02	3.75	3.35	2.81	3.13	5.6	80	130	Included	631-0000-004	631-0000-001
200	631-1506-000	14	4.36	4.50	3.98	2.81	3.75	7.7	80	130	Included	631-0000-004	631-0000-001
250	631-1606-000	14	4.36	4.50	3.98	3.19	3.75	8.3	80	130	Included	631-0000-004	631-0000-001
300	631-1706-000	14	4.74	4.50	3.98	3.19	3.75	9.7	80	130	Included	631-0000-004	631-0000-001
350	631-1806-000	14	5.75	4.50	3.98	4.72	3.75	10.4	80	130	Included	631-0000-004	631-0000-001
500	631-1906-000	14	6.11	5.25	4.64	4.38	4.38	14.5	80	130	Included	631-0000-006	631-0000-001
750	631-2006-000	14	7.61	5.25	4.64	5.87	4.38	27.6	80	130	Included	631-0000-006	631-0000-001
1000	631-2106-000	14	7.11	6.75	5.88	4.97	6.13	32.3	80	130	Included	631-0000-006	631-0000-001
1500	631-2206-000	15	7.38	6.75	5.75	4.25	6.13	40.7	115	180	Included	631-0000-006	631-0000-001
2000	631-2306-000	15	8.13	6.75	5.75	5.25	6.13	51.7	115	180	Included	631-0000-006	631-0000-001
3000	631-2406-001	15	8.56	9.00	7.50	5.75	7.50	77.1	115	180	NA	631-0000-006	NA
5000	631-2606-001	15	10.38	9.00	7.50	7.56	7.50	117.2	115	180		631-0000-006	

**Note:** Housing dimensions subject to change without notice. Consult website or factory where dimensions are critical.

\* Secondary fuse clips add 0.5" to C dimension.

