

The World's Most Specified Wire Cable Tray

Cablofil is the wire cable tray market leader with more than 80,000 miles installed worldwide. For over 30 years engineers and contractors around the world have found Cablofil to be the solution to any installation, large or small.

Cablofil Wire Cable Tray installs faster than traditional cable management methods. Every component of our product line has been designed to reduce installation time and costs. It can be configured to any installation, with simple tools, on the job site. Our Fast Installation System (FAS) line of mounting accessories can make installation even faster.

Cablofil products are available in a wide variety of tray sizes and finishes to meet any application need, from telecommunication systems to supporting power cables in harsh environments. To see the complete line of Cablofil products, visit our updated website at www.cablofil.com.



CABLOFIL
INNOVATORS IN CABLE MANAGEMENT



Electrical Power Cable Support



Telecommunications Installation



Instrumentation for Industry

THE WORLD'S MOST SPECIFIED WIRE CABLE TRAY

Ever since we invented the wire cable tray industry more than 30 years ago, we have focused on developing products that **save both time and money**. To support this effort Cablofil offers engineering services and are dedicated to helping our customers design the most efficient cable management system possible.

Visit our website to download Cablofil "**CSI Three Part**" specifications in word or pdf format.

Cablofil® Wire Cable Tray

Available in 10' straight sections, Cablofil wire cable tray is available in a variety of sizes and finishes to suit any application. Our unique Safe-T-Edge design eliminates frayed cables.

CF 30 – CABLOFIL CABLE TRAY



	H		W		L		Weight	
	INCHES	MM	INCHES	MM	FEET	M	LBS	KG
ZF 30/50*	1"	30	2"	50	10'	3	3.3	1.5
CF 30/100	1"	30	4"	100	10'	3	4.5	2.0
CF 30/150	1"	30	6"	150	10'	3	5.7	2.6
CF 30/200	1"	30	8"	200	10'	3	7.4	3.3
CF 30/300	1"	30	12"	300	10'	3	9.4	4.3

CF 54 – CABLOFIL CABLE TRAY



	H		W		L		Weight	
	INCHES	MM	INCHES	MM	FEET	M	LBS	KG
CF 54/50	2"	54	2"	50	10'	3	5.3	2.4
CF 54/100	2"	54	4"	100	10'	3	6.5	3.0
CF 54/150	2"	54	6"	150	10'	3	7.8	3.5
CF 54/200	2"	54	8"	200	10'	3	9.0	4.1
CF 54/300	2"	54	12"	300	10'	3	13.4	6.1
CF 54/450	2"	54	18"	450	10'	3	22.8	10.3
CF 54/500	2"	54	20"	500	10'	3	24.4	11.0
CF 54/600	2"	54	24"	600	10'	3	27.5	12.5

CF 105 – CABLOFIL CABLE TRAY



	H		W		L		Weight	
	INCHES	MM	INCHES	MM	FEET	M	LBS	KG
CF 105/100	4"	105	4"	100	10'	3	9.0	4.1
CF 105/150	4"	105	6"	150	10'	3	10.2	4.6
CF 105/200	4"	105	8"	200	10'	3	13.4	6.1
CF 105/300	4"	105	12"	300	10'	3	21.2	9.6
CF 105/450	4"	105	18"	450	10'	3	25.9	11.8
CF 105/500	4"	105	20"	500	10'	3	27.5	12.5
CF 105/600	4"	105	24"	600	10'	3	30.4	13.8

CF 150 – CABLOFIL CABLE TRAY



	H		W		L		Weight	
	INCHES	MM	INCHES	MM	FEET	M	LBS	KG
CF 150/300	6"	150	12"	300	10'	3	24.4	11.0
CF 150/450	6"	150	18"	450	10'	3	26.5	12.0
CF 150/500	6"	150	20"	500	10'	3	27.8	12.6
ZF 150/600	6"	150	24"	600	10'	3	29.5	13.4

All trays are offered in the following finishes:



Cablofil® Wire Cable Tray Connectors & Mounting Hardware

Cablofil has designed a wide range of easy-to-use connectors and supports including our Fast Assembly System (FAS) that simplify installations and reduce overall costs. To see the complete line of Cablofil products, visit our updated website at www.cablofil.com.

EDRN – FAST SPLICE



EDRN	50	LBS		KG	
		8.8	4.0		
EZ	DC	BL	PE		

- Fastest splice available from Cablofil, saves up to 1/2 the install time compared to using bolted connections.
- Special assembly tool (EDRNTOOL) is included in every bag of splices.

FASLOCK – SPLICE



FAS LOCK	25	LBS		KG	
		1.4	.63		
PG	DC	316L	BL	PE	

- Use to create sweeps and bends in Cablofil tray installations.
- Use pliers to bend locking tabs to secure FASLOCK.


EZT 90 KIT – 90° BEND KIT



EZT 90 KIT	LBS		KG	
	1.5	0.7		
EZ	GC	316L	BL	PE

- 1 Kit contains hardware for 1 tee or 2 90° bends.
- Slotted Design fits any size tray and eliminates precise tray alignment.

FAS U UNIVERSAL BRACKET




	INCHES		MM		INCHES		MM		LBS		KG	
	INCHES	MM	INCHES	MM	INCHES	MM	INCHES	MM	LBS	KG		
FASU 100	4"	100	6"	157	3.5"	85	0.3	0.1				
FASU 150	6"	150	8"	207	5.0"	124	0.4	0.2				
FASU 200	8"	200	12"	257	5.5"	139	0.5	0.2				
FASU 300	12"	300	14"	357	5.5"	139	0.8	0.3				
FASU 400	16"	400	18"	457	5.5"	137.7	1.8	0.8				
FASU 500	20"	500	22"	557	5.5"	137.7	2.9	1.3				
FASU 600	24"	600	26"	657	5.5"	137.7	6.4	2.9				

- Patented FAS style attachment holds cable tray secure without nuts and bolts.

Cablofil® Wire Cable Tray Connectors & Mounting Hardware (continued)

FAS PCH – CENTER HANGER



- Only one threaded rod is needed to suspend tray.
- Suspension tube protects cables.
- 18" Center Hanger has offset suspension tube to avoid center wire.
- Threaded rod, nuts and washers sold separately.

	INCHES	MM	LBS	KG
FASPCH 200	8"	194	0.7	0.3
FASPCH 300	12"	294	0.9	0.4
FASPCH 400	16"	394	1.1	0.5
FASPCH 450	18"	444	1.3	0.6
FASPCH 500	20"	494	1.3	0.6
FASPCH 600	24"	594	1.5	0.7

PG GC 316L BL PE

AS – TRAPEZE HANGING CLIP



		LBS	KG
AS	50	6.6	3.0

PG GC 316L BL PE

- Tray can be detached on one side to add cables.
- Use pliers to lock tabs and secure tray to threaded rod.
- Threaded rods, nuts, and washers sold separately.

UFC – UNDER FLOOR SUPPORT CLAMP



	INCHES	MM	LBS/1	KG/1
UFC	5"	127	0.7	0.3

PG BL PE

- Attaches FAS L Brackets to access floor posts through one side of U-Bolt.
- Unique support plate works with square or round posts.
- Clamp Kit contains: U Bolt, 2 flange nuts, and support plate.

For information on additional Cablofil Products: www.cablofil.com • 800-658-4641 or 618-566-3230 • fax: 618-566-3250 • info@cablofil.com

FINISHES

Cablofil wire cable tray and accessories are available in a variety of finishes to meet any industry need, from decorative to extreme environments. Use this color code to help you to determine the best finish for your application and its availability.

PG Pre-Galvanized – Continuous Galvanization Before Fabrication	304L Stainless Steel 304L –	BL Black Painted – Black Powder Coated
EZ Electrozinc – Electrozinc plating	316L Stainless Steel 316L –	PE Custom Painted – Custom Color Powder Coated
GC Hot Dipped Galvanized – After Fabrication	DC Dacromet – Zinc and Aluminum Protection Equivalent to Hot Dip Galvanization	

TESTED

Cablofil products have been independently evaluated to meet applicable standards and requirements.



legrand®

CABLOFIL®

INNOVATORS IN CABLE MANAGEMENT

8319 State Route 4 • Mascoutah, IL 62258
1-800-658-4641 • 618-566-2320 • FAX 618-566-3250

