

cmNpYWwvbGF5ZXIItemVyby1zb2x1dGlbnMuYXNweGQWAmYPFglfAAUUTGF5ZXIlgWmVybyBTb2x1dGlbnNkAggPZBYCAgEPDxYCHwQFFy9jb21tZXJje



designed to be better.

Search

# Commerical Specification Grade Switch, Light Almond

CS15AC1LA  
Commercial 1pole Switch, Side Wire, 15amp 120/277volt, Light Almond.

Submit Query

Where to buy

Submit Query

Like 0 Tweet 0

0  
Email Print





•

•

## product gallery

Representative images shown.

### AVAILABLE OPTIONS

Commerical Specification Grade Switches, White

Commerical Specification Grade Switch, Brown

Commerical Specification Grade Switch, Black

Commerical Specification Grade Switch, Gray

Commerical Specification Grade Switch, Ivory

- SPECIFICATIONS
- RESOURCES

### features & benefits

- One-piece brass alloy contact arm for reliable electrical performance.
- One-piece steel strap with integral ground is plated for corrosion resistance.
- High strength thermoplastic polycarbonate toggle resists breaking and chipping under heavy abuse.
- Heavy-duty toggle bumpers for smooth and quiet operation.
- Back body made of glass-reinforced nylon. Locking support provides resistance to face and back body separation.
- Available with side wire or external screw-pressure-plate back and side wire models capable of accepting #14 - #10 AWG copper or copper-clad wire.
- Cam designed for fast make with positive break action to minimize arcing and prolong switch life.
- Oversized silver alloy contacts for longer dependable switch life.
- Tri-drive terminal and mounting screws.

### Top 5 Resources

-  Commercial & Industrial Products (Brochure)
-  Commercial Grade Switches, SF105R2 (Cutsheet)

## specifications

### General Info

- Color: Light Almond
- Type: Side Wire
- Duty: Heavy Duty
- Number Of Poles: 1

### Listing Agencies/Third Party Information

- CSA Listing Info: C22.2 111
- CSA Standard: Yes
- Federal Spec: Yes
- Fed Spec Number: W5896
- UL Listing No: 20
- UL Standard: Yes
- U N SPS C: 39121507

### Dimensions

- Depth (U S): 1.073"
- Height U S: 3.281"
- Width U S: 1.320"

### Technical Information

- Amps: 15 Amp
- Volts: 120/277VAC
- Volts A C: 120/277
- Grade Type: Commercial

### Buy American Act Compliance

- Country of Origin: MEXICO
- Buy American Act Status: Trade Agreement Act Compliant
- 

## resources

### BROCHURE

 Commercial & Industrial ProductsPDF (3.52mb)

### CUTSHEET

 Commercial Grade Switches, SF105R2PDF (273.29kb)