

tZWRpYS8xNEE0RjIDNjExNzA0NUJDOTE3Qzk0NEJFMDFGRkMyNi5hc2h4ZAIFDw8WBB8ABR1WaWV3IHRoZSBEZWNvcnF0b3lgQ29sbGVjdGlvbh8EBS



designed to be better.

Search

# Hard Use Specification Grade Switch, Light Almond

CSB15AC4LA

Construction 4way Switch, Back & Side Wire, 15amp 120/277volt, Light Almond.

Submit Query

Where to buy

Submit Query

0

Email Print



Representative image shown.

## AVAILABLE OPTIONS



Hard Use Specification Grade Switch, White



Hard Use Specification Grade Switch, Brown



Hard Use Specification Grade Switch, Gray



Hard Use Specification Grade Switch, Ivory



- SPECIFICATIONS
- RESOURCES

## features & benefits

- One-piece brass alloy contact arm for reliable electrical performance.
- One-piece steel strap with integral ground is plated for corrosion resistance.
- High strength thermoplastic polycarbonate toggle resists breaking and chipping under heavy abuse.
- Heavy-duty toggle bumpers for smooth and quiet operation.
- Back body made of glass-reinforced nylon. Locking support provides resistance to face and back body separation.
- Available with side wire or external screw-pressure-plate back and side wire models capable of accepting #14 - #10 AWG copper or copper-clad wire.
- Cam designed for fast make with positive break action to minimize arcing and prolong switch life.

- Oversized silver alloy contacts for longer dependable switch life.
- Tri-drive terminal and mounting screws.

#### Top 5 Resources

-  Commercial & Industrial Products (Brochure)
-  Hard Use Switches, SF104R2 (Cutsheet)

#### specifications

##### General Info

- Color: Light Almond
- Duty: Hard Use
- Number Of Poles: 4-way

##### Listing Agencies/Third Party Information

- CSA Listing Info: C22.2 111
- CSA Standard: Yes
- Federal Spec: Yes
- Fed Spec Number: WS896
- UL Listing No: 20
- UL Standard: Yes
- U N SPS C: 39121507

##### Dimensions

- Depth (U S): 1.073"
- Height U S: 3.281"
- Width U S: 1.320"

##### Technical Information


- Amps: 15 Amp
- Volts: 120/277VAC
- Volts A C: 120/277
- Grade Type: Specification

##### Buy American Act Compliance


- Country of Origin: MEXICO
- Buy American Act Status: Trade Agreement Act Compliant
- 



#### resources BROCHURE

-  Commercial & Industrial ProductsPDF (3.52mb)

#### CUTSHEET

-  Hard Use Switches, SF104R2PDF (275.93kb)