

eCl+PHNwYW4gc3R5bGU9ImZvbnQtc2l6ZTogMTJweDsiPlZJRvcgQUxMPC9zcGFuPjwvYT48L2Rpdj4gPHVsiHN0eWxiPSJ3aWR0aDogMTgzcHg7IGZsb2F



designed to be better.

Search

# Hard Use Specification Grade Switch, Ivory

CSB20AC11

Construction 1pole Switch, Back & Side Wire, 20amp 120/277volt, Ivory.

Submit Query

Where to buy

Submit Query

0

Email Print



Representative image shown.

## AVAILABLE OPTIONS



Hard Use Specification Grade Switch, White



Hard Use Specification Grade Switch Brown



Hard Use Specification Grade Switch, Black



Hard Use Specification Grade Switch, Gray



Hard Use Specification Grade Switch, Light Almond



• SPECIFICATIONS

- RESOURCES

## features & benefits

- One-piece brass alloy contact arm for reliable electrical performance.
- One-piece steel strap with integral ground is plated for corrosion resistance.
- High strength thermoplastic polycarbonate toggle resists breaking and chipping under heavy abuse.
- Heavy-duty toggle bumpers for smooth and quiet operation.
- Back body made of glass-reinforced nylon. Locking support provides resistance to face and back body separation.
- Available with side wire or external screw-pressure-plate back and side wire models capable of accepting #14 - #10 AWG copper or copper-clad wire.
- Cam designed for fast make with positive break action to minimize arcing and prolong switch life.
- Oversized silver alloy contacts for longer dependable switch life.
- Tri-drive terminal and mounting screws.

## Top 5 Resources

-  Commercial & Industrial Products (Brochure)
-  Hard Use Switches, SF104R2 (Cutsheet)

## specifications

### General Info

- Color: Ivory
- Duty: Hard Use
- Number Of Poles: 1

### Listing Agencies/Third Party Information

- CSA Listing Info: C22.2 111
- CSA Standard: Yes
- Federal Spec: Yes
- Fed Spec Number: WS896
- UL Listing No: 20
- UL Standard: Yes
- U N SPS C: 39121507

### Dimensions

- Depth (U S): 1.073"
- Height U S: 3.281"
- Width U S: 1.320"

## Technical Information

- Amps: 20 Amp
- Volts: 120/277VAC
- Volts A C: 120/277
- Grade Type: Specification

## Buy American Act Compliance

- Country of Origin: MEXICO
- Buy American Act Status: Trade Agreement Act Compliant
- 




## resources

### BROCHURE

-  Commercial & Industrial ProductsPDF (3.52mb)

### CUTSHEET

-  Hard Use Switches, SF104R2PDF (275.93kb)