

xpbWcgcmVwbGFjZT0iZHNyYyIlgZHNyYz0iL34vbWVkaWEvQ0ZGNUMVERDc1MDQ4NEVEQTg4NzdDNjVDNzBGMDRBRTYuYXNoeClgYWx0PSJVbmRlci1E



designed to be better.

 Search

15 Amp NEMA L515 Single Receptacle, Orange, Isolated Ground

IG4710

Turnlok Single Receptacle 3wire 15amp 125volt Isolated Ground

Where to buy

0



Representative image shown.

- SPECIFICATIONS
- RESOURCES

features & benefits

- UL1449 (latest revision). (1.2 x 50µs 6000V, 8 x 20µs 3000A).
- 140 joules of energy absorption in each of the three modes.
- 9,000 amps current handling capability in each of three modes; line to neutral, line to ground, neutral to ground.
- 1 filtering capacitor for 7 to 1 average noise reduction.
- Nominal let-through (suppressed) voltage in all 3 modes, 500V.
- LED indicator light.
- Response time less than 1 nanosecond for unmounted MOV.
- Overcurrent protection in all 3 modes.
- Electronic components potted for electrical, mechanical and thermal stability.
- Thermal protection in all 3 modes.
- Leakage current: 0.5 mA at 25°C/120VAC.
- 3 18mm super MOVs to suppress transients in all modes – equally.
- Common mode noise attenuation: 500 KHz to 30 MHz; up to 35 dB(50 ohm source impedance)
- Varistor voltage: 150V RMS.
- Back and side wire capability including ground terminal.
- Operating temperature: -40°C to 85°C(-40°F to 185°F)
- Conforms to the latest revision ANSI/IEEE C62.41 (formerly IEEE 587), ANSI/IEEE C62.45.

Top 5 Resources

- Commercial & Industrial Products (Brochure)
- Turnlok Heavy Duty Isolated Ground Receptacles, SF1302R1 (Cutsheet)

specifications

General Info

- Type: Single, Receptacles
- Number Of Wires: 3
- Special Features: Isolated Ground

Listing Agencies/Third Party Information

- CSA Standard: Yes
- UL Listing No: 498
- UL Standard: Yes
- U N SPS C: 39121403

Dimensions

- Depth (U S): 1.0"
- Height U S: 3.281"
- Width U S: 1.437"

Technical Information

- Amps: 15 Amp
- NEMA Configuration Number: L515
- Volts: 125V

- Volts A C: 125

Buy American Act Compliance


- Country of Origin: MEXICO
- Buy American Act Status: Trade Agreement Act Compliant
-



resources BROCHURE

 Commercial & Industrial ProductsPDF (3.52mb)

CUTSHEET

 Turnlok Heavy Duty Isolated Ground Receptacles, SF1302R1PDF (2.24mb)