



designed to be better.

Search

20 Amp NEMA L620 Single Receptacle, Orange, Isolated Ground

IGL620R

Turnlok Receptacle Single 3wire 20amp 250volt Isolated Ground

Submit Query

Where to buy Enter Postal Code

Submit Query

0

Email Print



Representative image shown.



- SPECIFICATIONS
- RESOURCES

features & benefits

- UL1449 (latest revision). (1.2 x 50 μ s 6000V, 8 x 20 μ s 3000A).
- 140 joules of energy absorption in each of the three modes.
- 9,000 amps current handling capability in each of three modes; line to neutral, line to ground, neutral to ground.
- 1 filtering capacitor for 7 to 1 average noise reduction.
- Nominal let-through (suppressed) voltage in all 3 modes, 500V.
- LED indicator light.
- Response time less than 1 nanosecond for unmounted MOV.
- Overcurrent protection in all 3 modes.
- Electronic components potted for electrical, mechanical and thermal stability.
- Thermal protection in all 3 modes.
- Leakage current: 0.5 mA at 25°C/120VAC.

- 3 18mm super MOVs to suppress transients in all modes – equally.
- Common mode noise attenuation:500 KHz to 30 MHz; up to 35 dB(50 ohm source impedance)
- Varistor voltage: 150V RMS.
- Back and side wire capability including ground terminal.
- Operating temperature: -40°C to 85°C(-40°F to 185°F)
- Conforms to the latest revision ANSI/IEEE C62.41 (formerly IEEE 587), ANSI/IEEE C62.45.

Top 5 Resources

-  Commercial & Industrial Products (Brochure)
-  Turnlok Heavy Duty Isolated Ground Receptacles, SF1302R1 (Cutsheet)

specifications

General Info

- Color: Orange
- Type: Single, Receptacles
- Number Of Wires: 3
- Special Features: Isolated Ground

Listing Agencies/Third Party Information

- CSA Standard: Yes
- CUL Listing No: No
- cU Lus: No
- cU Rus: No
- UL Listing No: 498
- UL Standard: Yes
- U N SPS C: 39121403
- U R: No

Dimensions

- Depth (U S): 1.19"
- Height U S: 3.28"
- Width U S: 1.61"

Technical Information

- Amps: 20 Amp
- NEMA Configuration Number: L620
- Volts: 250V
- Volts A C: 250

Buy American Act Compliance

- Country of Origin: MEXICO
- Buy American Act Status: Trade Agreement Act Compliant
-




resources

BROCHURE

 Commercial & Industrial ProductsPDF (3.52mb)

CUTSHEET

 Turnlok Heavy Duty Isolated Ground Receptacles, SF1302R1PDF (2.24mb)