

1OT12QzY4MkY2OEMyMDg2Qy5hc2h4IiBhbHQ9IldpcmVklE5ldHdvcmtzIiB3aWR0aD0iMjE4IiBoZWlnaHQ9IjExMilgZ5kAgUPDxYCHwQFH9uZXR3b3JraW:



designed to be better.

Search

## 30 AMP L1430 Turnlok Locking Plug

L1430P

Turnlok Plug 4wire 30amp 125/250v

Submit Query

Where to buy

Submit Query

0



Representative image shown.

- SPECIFICATIONS
- YOU MIGHT LIKE
- RESOURCES

### features & benefits

- Quick-thread assembly screws and cord-grip screws come backed-out, ready-to-wire.
- Industrial-strength, brass alloy plug blades and connector contacts resist heat rise, provide excellent conductivity.
- Raised ribs provide non-slip gripping profile for turning to lock and unlock.
- Double dovetail design provides superior protection against cord pull-out forces.
- Impact- and corrosion-resistant durable nylon 6/6 shell material.
- Rounded back contour reduces snags and hang-ups on the job site.
- Scallop shell design provides non-slip gripping surface for insertion and withdrawal.
- Visible stamped NEMA configuration and device rating.
- New-design external cord grips provide visible assurance of safe and proper cord retention.
- Integral flexible rubber cord grommet conforms to and seals around SO cord to provide protection from oils, water, or chips entering wiring chamber.

### Top 5 Resources

- Turnlok EHU Plugs & Connectors 4 Wire, SF1704R1 (Cutsheet)
- Commercial & Industrial Products (Brochure)

### specifications

#### General Info

- Type: Turnlock, locking Plug

#### Listing Agencies/Third Party Information

- CSA Standard: Yes
- Federal Spec: Yes
- Fed Spec Number: WC596
- UL Listing No: 498
- UL Standard: Yes
- U N SPS C: 39121403

#### Dimensions

- Diameter U S: 2.20"
- Length: 3.75"

#### Technical Information

- Amps: 30 Amp
- NEMA Configuration Number: L1430
- Volts: 250V

#### Buy American Act Compliance

- Country of Origin: MEXICO
- Buy American Act Status: Trade Agreement Act Compliant



you might like



**Strain Relief Grips**

BOX40

[View Details](#)



**30 Amp NEMA L1430 Connector - Black Back, White Front Body**

L1430C

[View Details](#)

**resources**

**BROCHURE**

[Commercial & Industrial ProductsPDF \(3.52mb\)](#)

**CUTSHEET**

[Turnlok EHU Plugs & Connectors 4 Wire, SF1704R1PDF \(552.93kb\)](#)