

aHgilGFsdD0iVXNlciBjbRlcmZhY2VzliB3aWR0aD0iMjE4IiBoZWlnaHQ9IjExMilgLz5kAgUPDxYCHwQFJS9ob21ILWF1dG9tYXRpb24vdXNlci1pbmRlcmZhY2



designed to be better.

 Search

## 20 Amp NEMA Plug L620 - Black Back, White Front Body

L620P

Turnlok Plug 3wire 20amp 250v

Where to buy 


0



Representative image shown.

- SPECIFICATIONS
- RESOURCES

### features & benefits

- Quick-thread assembly screws and cord-grip screws come backed-out, ready-to-wire.
- Industrial-strength, brass alloy plug blades and connector contacts resist heat rise, provide excellent conductivity.
- Raised ribs provide non-slip gripping profile for turning to lock and unlock.
- Double dovetail design provides superior protection against cord pull-out forces.
- Impact- and corrosion-resistant durable nylon 6/6 shell material.
- Rounded back contour reduces snags and hang-ups on the job site.
- Scallop shell design provides non-slip gripping surface for insertion and withdrawal.
- Visible stamped NEMA configuration and device rating.
- New-design external cord grips provide visible assurance of safe and proper cord retention.
- Integral flexible rubber cord grommet conforms to and seals around SO cord to provide protection from oils, water, or chips entering wiring chamber.

### Top 5 Resources

- [Turnlok EHU Plugs & Connectors 3 Wire, SF1702R2 \(Cutsheet\)](#)
- [Commercial & Industrial Products \(Brochure\)](#)

### specifications

#### General Info

- Color: Black, White
- Type: Plug
- Number Of Wires: 3

#### Listing Agencies/Third Party Information

- CSA Standard: Yes
- CUL Listing No: No
- cU Lus: Yes
- cU Rus: No
- Federal Spec: Yes
- Fed Spec Number: WC596
- UL Listing No: 498
- UL Standard: Yes
- U N SPS C: 39121403
- U R: No

#### Dimensions

- Depth (U S): 2.20"
- Length: 2.57"

#### Technical Information

- Amps: 20 Amp
- NEMA Configuration Number: L620
- Volts: 250V
- Volts A C: 250

**Buy American Act Compliance**


- Country of Origin: MEXICO
- Buy American Act Status: Trade Agreement Act Compliant
- 



**resources**  
**BROCHURE**

 Commercial & Industrial ProductsPDF (3.52mb)

**CUTSHEET**

 Turnlok EHU Plugs & Connectors 3 Wire, SF1702R2PDF (309.83kb)