

Qjg1MTI0QS5hc2h4liAvPmQCAw9kFgYCAQ8WAh8BZxYCAgEPFgfAwIFFgpmD2QWBgIBDw8WBB8EBSEvZGVzaWduZXItY29sbGVjdGlbnMvYWRvcm5ll



designed to be better.

[Search](#)

30 Amp NEMA L630 Plug - Black Back, White Front Body

L630P

Turnlok Plug 3wire 30amp 250v

[Submit Query](#)

Where to buy

[Submit Query](#)

0



Representative image shown.

- [SPECIFICATIONS](#)
- [YOU MIGHT LIKE](#)
- [RESOURCES](#)

features & benefits

- Quick-thread assembly screws and cord-grip screws come backed-out, ready-to-wire.
- Industrial-strength, brass alloy plug blades and connector contacts resist heat rise, provide excellent conductivity.
- Raised ribs provide non-slip gripping profile for turning to lock and unlock.
- Double dovetail design provides superior protection against cord pull-out forces.
- Impact- and corrosion-resistant durable nylon 6/6 shell material.
- Rounded back contour reduces snags and hang-ups on the job site.
- Scallop shell design provides non-slip gripping surface for insertion and withdrawal.
- Visible stamped NEMA configuration and device rating.
- New-design external cord grips provide visible assurance of safe and proper cord retention.
- Integral flexible rubber cord grommet conforms to and seals around SO cord to provide protection from oils, water, or chips entering wiring chamber.

Top 5 Resources

- [Turnlok EHU Plugs & Connectors 3 Wire, SF1702R2 \(Cutsheet\)](#)
- [Commercial & Industrial Products \(Brochure\)](#)

specifications

General Info

- Color: Black, White
- Type: Plug
- Number Of Wires: 3

Listing Agencies/Third Party Information

- CSA Standard: Yes
- CUL Listing No: No
- cU Rus: No
- Federal Spec: Yes
- Fed Spec Number: WC596
- UL Listing No: 498
- UL Standard: Yes
- U N SPS C: 39121403
- U R: No

Dimensions

- Diameter U S: 2.20"
- Length: 3.75"

Technical Information

- Amps: 30 Amp
- NEMA Configuration Number: L630
- Volts: 250V
- Volts A C: 250

Buy American Act Compliance

- Country of Origin: MEXICO
- Buy American Act Status: Trade Agreement Act Compliant
-



you might like



30 Amp NEMA L630 Connector - Black Back, White Front Body

L630C

[View Details](#)



Heavy-Duty Ground Continuity Monitoring (GCM) Plug, Black & White

L630PGCM

[View Details](#)

resources
BROCHURE

[Commercial & Industrial ProductsPDF \(3.52mb\)](#)

CUTSHEET

[Turnlok EHU Plugs & Connectors 3 Wire, SF1702R2PDF \(309.83kb\)](#)