

# Data Communications

## Pass & Seymour® Workstation Solutions

### Innovate™ Jack Modules

- Universal design supports wither T568A or T568B. Easy-to-read color code wiring label
- Front-mount, click-in design removes easily for quick reconfiguration
- Built strong to stand up to repeated installations and removals
- Paired punchdown sequence makes 110-style termination fast and simple
- Provides TIA/EIA-568B.2 standards compliance



WESCO Part No.	Mfr.'s Model No.	Color
----------------	------------------	-------

#### RJ45 Category 6, T568A/B Universal Wiring

785007-26323	S68-BK	Black
785007-26324	S68-BL	Blue
785007-26325	S68-BR	Brown
785007-26326	S68-G	Green
785007-26327	S68-GRY	Gray
785007-26328	S68-I	Ivory
785007-26329	S68-LA	Light Almond
785007-26330	S68-OR	Orange
785007-26331	S68-P	Purple
785007-26332	S68-RED	Red
785007-26333	S68-W	White
785007-26334	S68-Y	Yellow

#### RJ45 Category 5e, T568A/B Universal Wiring

785007-65462	S58-BK	Black
785007-65439	S58-BL	Blue
785007-65940	S58-BR	Brown
785007-65441	S58-G	Green
785007-65442	S58-GRY	Gray
785007-65443	S58-I	Ivory
785007-65444	S58-LA	Light Almond
785007-65445	S58-OR	Orange
785007-65446	S58-P	Purple
785007-65447	S58-RED	Red
785007-65448	S58-W	White
785007-65449	S58-Y	Yellow

#### RJ-45 CAT3 Jack, T568A/B Wiring

785007-65437	S38-LA	Light Almond
--------------	--------	--------------

#### RJ25C (RJ12) 6P/6C USOC Wiring

785007-65450	S6U-GRY	Gray
785007-65451	S6U-I	Ivory
785007-65452	S6U-LA	Light Almond
785007-65453	S6U-W	White

#### Miscellaneous Jacks

785007-65433	S2BP-LA	Binding Post L/R
785007-65472	SBL10-LA	Blank Kit 10/Bag
785007-65479	SFF-LA	Bulkhead for Video
785007-02756	RFCEXT-LA	Recessed F-Connector External

### RJ45 Plugs

- RJ-45 plug works with either solid or stranded Cat5 cable

WESCO Part No.	Mfr.'s Model No.	Description
----------------	------------------	-------------

804428-00395	364405-01	RJ45 Plug, 25 per Bag
--------------	-----------	-----------------------

Pass & Seymour



### Activate™ UTP Modular Inserts

- Single or dual inserts
- Light almond color\*
- Choose Category 5e, Category 3, or a combination
- Snap-in, front-loading design



WESCO Part No.	Mfr.'s Model No.	Description
----------------	------------------	-------------

785007-26716	2A145-C5EU	2A Cat5e RJ45 Single Port, T568A/B
785007-26721	2A245-C5EU	2A Cat5e RJ45 Dual Port, T568A/B
785007-10604	2A112-U2	2A Cat3 RJ12 Single Port, USOC
785007-26726	2A145-C3U	2A Cat3 RJ45 Single Port, T568A/B
785007-10619	2A212-U2	2A Cat3 RJ12 Dual Port, USOC

### Activate Multimedia Inserts

- Single or dual inserts
- Light almond color\*
- Choose from fiber optic, coaxial, audio, video, and blanks
- Snap-in, front-loading design means easy installation



WESCO Part No.	Mfr.'s Model No.	Description
----------------	------------------	-------------

785007-90508	2A-BL	2A Blank
785007-90418	2A-1F	2A Single F Adapter
785007-90478	2A-2RCA	2A Dual RCA Audio
785007-10614	2A-1SVHSU	2A Super VHS
785007-90442	2A-2F	2A Dual F Adapter
785007-90466	2A-2RBBP	2A Dual 3-Way Binding Post Audio
785007-90490	2A-2SC	2A Duplex SC Ceramic Ferrule, Single/Multimode
785007-90496	2A-2ST-MM	2A Dual ST Multimode




## Pass & Seymour



### Activate Wallplates

- Compatible with Wiremold wire and cable management platforms
- Holds 3 Activate inserts
- Light almond color\*
- WallReady eliminates the need for box or bracket



WESCO Part No.	Mfr.'s Model No.	Description
----------------	------------------	-------------

785007-55055	AC-SWRP	Single-Gang Wall-Ready Faceplate
785007-07875	AC-SFP	Single-Gang Faceplate
785007-07880	AC-SAP	Single-Gang Angled Faceplate



### TradeMaster® DataCom Wallplates

- Use with Innovate snap-in jacks
- Color and style matched to Pass & Seymour wiring devices and TradeMaster wallplate
- Light almond color\*



WESCO Part No.	Mfr.'s Model No.	Description
----------------	------------------	-------------

785007-18108	TPD1-LA	1 Port Single-Gang Wallplate
785007-18112	TPD2-LA	2 Port Single-Gang Wallplate
785007-18116	TPD3-LA	3 Port Single-Gang Wallplate
785007-18120	TPD4-LA	4 Port Single-Gang Wallplate
785007-18124	TPD6-LA	6 Port Single-Gang Wallplate
785007-18128	TPD9-LA	9 Port Double-Gang Wallplate

### Assembled Telephone & CATV Wallplates

- Mar-resistant single-gang wallplates fit standard-size single-gang electrical box
- UL® Listed

WESCO Part No.	Mfr.'s Model No.	Color
----------------	------------------	-------

#### Single-Gang Wallplate with (1) RJ-11, 6-Position, 4-Conductor Telephone Jack

785007-24766	TPTE1-LA	Light Almond
785007-24767	TPTE1-I	Ivory
785007-24768	TPTE1-W	White

#### Wall-Mount Telephone Jack for Hanging Phones

785007-06108	WMTE14-W	White
--------------	----------	-------

#### Single-Gang w/(1) Threaded F-Type Coax Connector

785007-24751	TPCATV-LA	Light Almond
785007-24752	TPCATV-I	Ivory
785007-24753	TPCATV-W	White

\*Pass & Seymour/Legrand light almond matches Wiremold ivory

