



designed to be better.

# TradeMaster USB Charger with Tamper-Resistant Receptacle, Ivory

TM8USBICC6

2 Standard type A USB's, 2.1 A or 2100mA, 10.5 watts. Combination with Decorator Tamper-Resistant 15 A AC Receptacle, Ivory.

Where to buy

Like

Tweet







## product gallery

Representative images shown.

### AVAILABLE OPTIONS



TradeMaster USB Charger with Tamper-Resistant Receptacle, White



TradeMaster USB Charger with Tamper-Resistant Receptacle, Black



TradeMaster USB Charger with Tamper-Resistant Receptacle, Light Almond



TradeMaster USB Charger with Tamper-Resistant Receptacle, Nickel






TradeMaster USB Charger with Tamper-Resistant Receptacle, Titanium

- RELATED PRODUCTS
- SPECIFICATIONS
- YOU MIGHT LIKE
- RESOURCES

## features & benefits

- Meets 2008 National Electrical Code Tamper-Resistant requirements.
- Protects children: patented shutter system helps prevent improper insertion of foreign objects.
- High-impact resistant thermoplastic construction.
- Extra-long strap.
- Quickloop wire looping aid.
- Long-term blade retention.
- Longer tri-drive screws for easier 12 AWG looping.
- Extra-large circuit break-off tabs.
- Side-access push wire release.
- Ultrasonic welding of face to back body.
- Side wire accepts #12 – #14 AWG solid wire.
- Push wire accepts #14 AWG solid only.
- Superior protection than traditional outlet caps or protection plates.
- Low profile face.
- Traditional contoured face (3232 models).
- Self-grounding models provide automatic ground clip.

## Top 5 Resources

-  USB Charger Tamper-Resistant Receptacles (Sell Sheet)

## related products



### Screwless Decorator Openings, Plastic Subplate, One Gang, Ivory

SWP26I

[View Details](#)

## specifications

### General Info

- Color: Ivory
- Type: Tamper-Resistant

## Listing Agencies/Third Party Information

- ETL Listing No: 4001804
- ETL Standard: Yes
- UL Listing No: In Process

## Dimensions

- Depth (U S): 1.6"
- Height U S: 2.7"
- Width U S: 1.7"

## Technical Information

- Amps: 15 Amp

## Buy American Act Compliance

- Country of Origin: CHINA
- Buy American Act Status: No
- 

## you might like



### 2000TR Series Tamper-Resistant Multioutlet System

2000TR

[View Details](#)



### Metal Raceway

[View Details](#)

## resources

## SELL SHEET

 [USB Charger Tamper-Resistant ReceptaclesPDF \(503.04kb\)](#)