


# Decorator Devices TradeMaster® Decorator Combination Switches


15A, 120VAC




Features	
<ul style="list-style-type: none"> <li>■ Impact-resistant face and body.</li> <li>■ Fully rounded back body protects wires from being damaged by sharp edges.</li> <li>■ Clear identification of circuits.</li> <li>■ External screw-pressure-plate back and side wired. Accepts #12 and #14 AWG.</li> <li>■ Ground screw position under the end of the strap minimizes the risk of contact.</li> <li>■ Full wraparound metal strap with lock-in tabs.</li> </ul>	<ul style="list-style-type: none"> <li>■ Patented split circuit tab – easily accessible, and can be reinstalled without a tool.</li> <li>■ Unique “Up/Down” switches match the look and feel of standard Decorator switches.</li> <li>■ Largest breadth of 15 amp offering.</li> <li>■ All screws are tri-drive.</li> <li>■ Tamper-resistant version features dual mechanical shutter system to help prevent insertion of foreign objects (see Page D-12).</li> </ul>



TM811WCC



TM811WCC



TM8111WCC

Catalog Number	Rating A. VAC	Color	3rd Party Compliance	
			UL <sub>20</sub>	cUL <sub>us</sub>
<b>Two Single Pole Switches</b>				
TM811ICC	15 120	Ivory	•	•
TM811WCC	15 120	White	•	•
TM811CC	15 120	Brown	•	•
TM811BKCC	15 120	Black	•	•
TM811LACC	15 120	Light Almond	•	•
<b>Single Pole Switch &amp; Three-Way Switch</b>				
TM813ICC	15 120	Ivory	•	•
TM813WCC	15 120	White	•	•
TM813CC	15 120	Brown	•	•
TM813BKCC	15 120	Black	•	•
TM813LACC	15 120	Light Almond	•	•
<b>Two Three-Way Switches</b>				
TM833ICC	15 120	Ivory	•	•
TM833WCC	15 120	White	•	•
TM833CC	15 120	Brown	•	•
TM833BKCC	15 120	Black	•	•
TM833LACC	15 120	Light Almond	•	•
<b>Three Single Pole Switches</b>				
TM8111ICC	15 120	Ivory	•	•
TM8111WCC	15 120	White	•	•
TM8111CC	15 120	Brown	•	•
TM8111BKCC	15 120	Black	•	•
TM8111LACC	15 120	Light Almond	•	•
<b>Two Single Pole Switches &amp; Three-Way Switch</b>				
TM8113ICC	15 120	Ivory	•	•
TM8113WCC	15 120	White	•	•
TM8113CC	15 120	Brown	•	•
TM8113BKCC	15 120	Black	•	•
TM8113LACC	15 120	Light Almond	•	•
<b>Four Single Pole Switches</b>				
TM811111ICC	15 120	Ivory	•	•
TM811111WCC	15 120	White	•	•
TM811111CC	15 120	Brown	•	•
TM811111BKCC	15 120	Black	•	•
TM811111LACC	15 120	Light Almond	•	•

All devices listed on this page conform to NEMA WD-1 and WD-6.