


# Switches TradeMaster® Decorator Illuminated & Self-Grounding Switches


15A, 120 & 120/277VAC



- | Features   |   |
|--|---|
| <ul style="list-style-type: none"> <li>■ Designer-style satin-finish rocker.</li> <li>■ High-impact resistant thermoplastic construction.</li> <li>■ External screw-pressure-plate back and side wired. Accepts #12 and #14 AWG.</li> <li>■ Push wire #14 AWG.</li> <li>■ Narrow back body leaves more room for wires in the box.</li> </ul> | <ul style="list-style-type: none"> <li>■ Extra-long, through-body strap eliminates floating installations and imperfect applications.</li> <li>■ Smooth, quiet paddle action.</li> <li>■ Easy-access green hex head ground screw.</li> <li>■ Tri-drive ground, terminal and mounting screws.</li> <li>■ Self-grounding models provide automatic ground clip.</li> </ul> |



TM870LASL



TM870SLA

| Catalog Number   | Rating<br>A. VAC | Color        | 3rd Party Compliance |           |
|--|------------------|--------------|----------------------|-----------|
|  |                  |              | UL 20                | C22.2 111 |
| <b>Single Pole Illuminated Decorator Switches</b> Grounding (Lighted when OFF) |                  |              |                      |           |
| TM870ISL   | 15 120           | Ivory        | •                    | •         |
| TM870WSL   | 15 120           | White        | •                    | •         |
| TM870LASL  | 15 120           | Light Almond | •                    | •         |
| <b>Self-Grounding Single Pole Decorator Switches</b>                           |                  |              |                      |           |
| TM870SI  | 15 120/277       | Ivory        | •                    | •         |
| TM870SW  | 15 120/277       | White        | •                    | •         |
| TM870S   | 15 120/277       | Brown        | •                    | •         |
| TM870SBK   | 15 120/277       | Black        | •                    | •         |
| TM870SLA   | 15 120/277       | Light Almond | •                    | •         |
| <b>Three-Way Illuminated Decorator Switches</b> Grounding (Lighted when OFF)   |                  |              |                      |           |
| TM873ISL   | 15 120           | Ivory        | •                    | •         |
| TM873WSL   | 15 120           | White        | •                    | •         |
| TM873LASL  | 15 120           | Light Almond | •                    | •         |
| <b>Self-Grounding Three-Way Decorator Switches</b>                             |                  |              |                      |           |
| TM873SI  | 15 120/277       | Ivory        | •                    | •         |
| TM873SW  | 15 120/277       | White        | •                    | •         |
| TM873S   | 15 120/277       | Brown        | •                    | •         |
| TM873SBK   | 15 120/277       | Black        | •                    | •         |
| TM873SLA   | 15 120/277       | Light Almond | •                    | •         |
| <b>Four-Way Illuminated Decorator Switches</b> Grounding (Lighted when OFF)    |                  |              |                      |           |
| TM874ISL   | 15 120           | Ivory        | •                    | •         |
| TM874WSL   | 15 120           | White        | •                    | •         |
| TM874LASL  | 15 120           | Light Almond | •                    | •         |
| <b>Self-Grounding Four-Way Decorator Switches</b>                              |                  |              |                      |           |
| TM874SI  | 15 120/277       | Ivory        | •                    | •         |
| TM874SW  | 15 120/277       | White        | •                    | •         |
| TM874S   | 15 120/277       | Brown        | •                    | •         |
| TM874SBK   | 15 120/277       | Black        | •                    | •         |
| TM874SLA   | 15 120/277       | Light Almond | •                    | •         |

All devices listed on this page conform to NEMA WD-1 and WD-6.