

# Switches TradeMaster® Decorator Combination Switches

15A, 120VAC


Pass & Seymour




## Features

- Impact-resistant face and body.
- Fully rounded back body protects wires from being damaged by sharp edges.
- Clear identification of circuits.
- External screw-pressure-plate back and side wired. Accepts #12 and #14 AWG.
- Ground screw position under the end of the strap minimizes the risk of contact.
- Full wraparound metal strap with lock-in tabs.
- Patented split circuit tab – easily accessible, and can be reinstalled without a tool.
- Unique “Up/Down” switches match the look and feel of standard Decorator switches.
- Largest breadth of 15 amp offering.
- All screws are tri-drive.
- Patented Snap-In Light and Identification Modules (sold separately). See Page A-20 for details.


Catalog Number	Rating A. VAC	Color	3rd Party Compliance	
			UL <sup>®</sup> UL20	cULus cULus
<b>Two Single Pole Switches</b>				
TM811-ICC	15 120	Ivory	•	•
TM811-WCC	15 120	White	•	•
TM811-CC	15 120	Brown	•	•
TM811-BKCC	15 120	Black	•	•
TM811-LACC	15 120	Light Almond	•	•
<b>Two Single Pole Switches with Pilot Light</b>				
TM811-PLICC	15 120	Ivory	•	•
TM811-PLWCC	15 120	White	•	•
TM811-PLBKCC	15 120	Black	•	•
TM811-PLLACC	15 120	Light Almond	•	•
<b>Single Pole Switch &amp; Three-Way Switch</b>				
TM813-ICC	15 120	Ivory	•	•
TM813-WCC	15 120	White	•	•
TM813-CC	15 120	Brown	•	•
TM813-BKCC	15 120	Black	•	•
TM813-LACC	15 120	Light Almond	•	•
<b>Single Pole Switch with Pilot Light &amp; Three-Way Switch</b>				
TM813-PLICC	15 120	Ivory	•	•
TM813-PLWCC	15 120	White	•	•
TM813-PLBKCC	15 120	Black	•	•
TM813-PLLACC	15 120	Light Almond	•	•
<b>Two Three-Way Switches</b>				
TM833-ICC	15 120	Ivory	•	•
TM833-WCC	15 120	White	•	•
TM833-CC	15 120	Brown	•	•
TM833-BKCC	15 120	Black	•	•
TM833-LACC	15 120	Light Almond	•	•
<b>Three Single Pole Switches</b>				
TM8111-ICC	15 120	Ivory	•	•
TM8111-WCC	15 120	White	•	•
TM8111-CC	15 120	Brown	•	•
TM8111-BKCC	15 120	Black	•	•
TM8111-LACC	15 120	Light Almond	•	•
<b>Two Single Pole Switches &amp; Three-Way Switch</b>				
TM8113-ICC	15 120	Ivory	•	•
TM8113-WCC	15 120	White	•	•
TM8113-CC	15 120	Brown	•	•
TM8113-BKCC	15 120	Black	•	•
TM8113-LACC	15 120	Light Almond	•	•
<b>Four Single Pole Switches</b>				
TM81111-ICC	15 120	Ivory	•	•
TM81111-WCC	15 120	White	•	•
TM81111-CC	15 120	Brown	•	•
TM81111-BKCC	15 120	Black	•	•
TM81111-LACC	15 120	Light Almond	•	•



TM811-WCC



TM8111-WCC



TM81111-WCC

All devices listed on this page conform to NEMA WD-1 and WD-6.