


Switches TradeMaster® Decorator Combination Switches


15A, 120VAC




- | Features | |
|---|---|
| <ul style="list-style-type: none"> ■ Impact-resistant face and body. ■ Fully rounded back body protects wires from being damaged by sharp edges. ■ Clear identification of circuits. ■ External screw-pressure-plate back and side wired. Accepts #12 and #14 AWG. ■ Ground screw position under the end of the strap minimizes the risk of contact. ■ Full wraparound metal strap with lock-in tabs. | <ul style="list-style-type: none"> ■ Patented split circuit tab – easily accessible, and can be reinstalled without a tool. ■ Unique “Up/Down” switches match the look and feel of standard Decorator switches. ■ Largest breadth of 15 amp offering. ■ All screws are tri-drive. ■ Tamper-resistant version features dual mechanical shutter system to help prevent insertion of foreign objects (see Page A-26). |



TM811WCC



TM8111WCC



TM81111WCC

Catalog Number	Rating A. VAC	Color	3rd Party Compliance	
			UL20	cULus
Two Single Pole Switches				
TM811ICC	15 120	Ivory	•	•
TM811WCC	15 120	White	•	•
TM811CC	15 120	Brown	•	•
TM811BKCC	15 120	Black	•	•
TM811LACC	15 120	Light Almond	•	•
Single Pole Switch & Three-Way Switch				
TM813ICC	15 120	Ivory	•	•
TM813WCC	15 120	White	•	•
TM813CC	15 120	Brown	•	•
TM813BKCC	15 120	Black	•	•
TM813LACC	15 120	Light Almond	•	•
Two Three-Way Switches				
TM833ICC	15 120	Ivory	•	•
TM833WCC	15 120	White	•	•
TM833CC	15 120	Brown	•	•
TM833BKCC	15 120	Black	•	•
TM833LACC	15 120	Light Almond	•	•
Three Single Pole Switches				
TM8111ICC	15 120	Ivory	•	•
TM8111WCC	15 120	White	•	•
TM8111CC	15 120	Brown	•	•
TM8111BKCC	15 120	Black	•	•
TM8111LACC	15 120	Light Almond	•	•
Two Single Pole Switches & Three-Way Switch				
TM8113ICC	15 120	Ivory	•	•
TM8113WCC	15 120	White	•	•
TM8113CC	15 120	Brown	•	•
TM8113BKCC	15 120	Black	•	•
TM8113LACC	15 120	Light Almond	•	•
Four Single Pole Switches				
TM81111ICC	15 120	Ivory	•	•
TM81111WCC	15 120	White	•	•
TM81111CC	15 120	Brown	•	•
TM81111BKCC	15 120	Black	•	•
TM81111LACC	15 120	Light Almond	•	•

All devices listed on this page conform to NEMA WD-1 and WD-6.