



designed to be better.

TradeMaster Decorator Switch, Ivory

TM874I

Decorator Switch, 4Way 15Amp 120/277V, Ivory

Where to buy

Like

Tweet

 
Email Print



product gallery

Representative images shown.

AVAILABLE OPTIONS



TradeMaster Decorator Switch, White



TradeMaster Decorator Switch, Brown



TradeMaster Decorator Switch, Black



TradeMaster Decorator Switch, Gray



TradeMaster Decorator Switch, Ivory



TradeMaster Single Pole Illuminated Decorator Switch, Ivory



TradeMaster Decorator Switch, Light Almond





TradeMaster Single Pole Illuminated Decorator Switch, Light Almond



Nickel Decorator Switch



TradeMaster Decorator Switch, Titanium



TradeMaster Decorator Switch, White



TradeMaster Single Pole Illuminated Decorator Switch, White



TradeMaster Decorator Switch, Brown





TradeMaster Decorator Switch, Black



TradeMaster Decorator Switch, Gray



TradeMaster Decorator Switch, Ivory



TradeMaster Three-Way Illuminated Decorator Switch, Ivory



TradeMaster Decorator Switch, Light Almond



TradeMaster Three-Way Illuminated Decorator Switch, Light Almond





Nickel Decorator Switch



TradeMaster Self-Grounding Three-Way Decorator Switch, Brown



TradeMaster Self-Grounding Three-Way Decorator Switch, Black



TradeMaster Self-Grounding Three-Way Decorator Switch, Ivory



TradeMaster Self-Grounding Three-Way Decorator Switch, Light Almond



TradeMaster Self-Grounding Three-Way Decorator Switch, White





TradeMaster 3-Way Decorator Switch, Titanium



TradeMaster Decorator Switch, White



TradeMaster Decorator Switch, White



TradeMaster Decorator Switch, White



TradeMaster Three-Way Illuminated Decorator Switch, White



TradeMaster Three-Way Illuminated Decorator Switch, White



TradeMaster Decorator Switch, Brown



TradeMaster Decorator Switch, Brown



TradeMaster Decorator Switch, Black



TradeMaster Decorator Switch, Black



TradeMaster Four-Way Illuminated Decorator Switches, Ivory



TradeMaster Decorator Switch, Light Almond



TradeMaster Four-Way Illuminated Decorator Switches, Light Almond



Nickel Decorator Switch



TradeMaster Self-Grounding Four-Way Decorator Switch, Brown



TradeMaster Self-Grounding Four-Way Decorator Switch, Black



TradeMaster Self-Grounding Four-Way Decorator Switch, Ivory





TradeMaster Self-Grounding Four-Way Decorator Switch, Light Almond



TradeMaster Self-Grounding Four-Way Decorator Switch, White



Titanium Decorator Switch



TradeMaster Decorator Switch, White



TradeMaster Four-Way Illuminated Decorator Switches, White



Decorator Home Locator Switch, Ivory





Decorator Home Locator Switch, Light Almond



Decorator Home Locator Switch, White

- SPECIFICATIONS
- RESOURCES

specifications

General Info

- Product Series: TradeMaster
- Number Of Poles: 4-way
- Special Features: Self-Grounding
- Style: Decorator

Listing Agencies/Third Party Information

- CSA Listing Info: C22.2 111
- CSA Standard: Yes
- UL Listing No: 20
- UL Standard: Yes
- U N SPS C: 39121704

Dimensions

- Depth (U S): 1.27'
- Height U S: 4.19"
- Width U S: 1.43"

Technical Information

- Amps: 15 Amp
- Volts: 120/277VAC
- Volts A C: 120/277

Buy American Act Compliance

- Country of Origin: MEXICO
- Buy American Act Status: Buy American Act Compliant
-



resources

SUPPORTING DOCUMENT

 NAFTA Compliant Residential DevicesPDF (366.4kb)