


# Wall Plates Communication Devices


Telephone & CATV Wiring Devices



Features	
<ul style="list-style-type: none"> <li>Mar-resistant wall plate.</li> <li>Fits standard size single gang electrical box.</li> <li>Wall plate dimension is Standard size.</li> </ul>	<ul style="list-style-type: none"> <li>Nickel-plated steel.</li> <li>Connector is threaded at each end.</li> </ul>



TPCATV




TPCATV2


Catalog Number	Color	Configuration	3rd Party Compliance UL1863
<b>“F” Type with One Coaxial Connector &amp; Wall Plate, Single Gang</b>			
TPCATVI	Ivory	F-type COAX Connector	•
TPCATVW	White	F-type COAX Connector	•
TPCATV	Brown	F-type COAX Connector	•
TPCATVBK	Black	F-type COAX Connector	•
TPCATVLA	Light Almond	F-type COAX Connector	•
<b>“F” Type with Two Coaxial Connectors &amp; Wall Plate, Single Gang</b>			
TPCATV2I	Ivory	2 F-type COAX Connectors	•
TPCATV2W	White	2 F-type COAX Connectors	•
TPCATV2	Brown	2 F-type COAX Connectors	•
TPCATV2BK	Black	2 F-type COAX Connectors	•
TPCATV2LA	Light Almond	2 F-type COAX Connectors	•

Features	
<ul style="list-style-type: none"> <li>Decorator outline.</li> <li>Face constructed of high-impact thermoplastic.</li> <li>Zinc-plated steel strap.</li> </ul>	<ul style="list-style-type: none"> <li>Nickel-plated “F” type connector.</li> <li>Threaded on each end.</li> </ul>

Catalog Number	Color	Configuration	3rd Party Compliance UL1863
<b>Decorator “F” Type Coaxial Connector</b> Single Gang with 1 COAX Connector			
26CATVI	Ivory	F-type COAX Connector	•
26CATVW	White	F-type COAX Connector	•
26CATVLA	Light Almond	F-type COAX Connector	•




26CATV



TPTELTV

Features	
<ul style="list-style-type: none"> <li>Decorator outline.</li> <li>RJ11 modular jack.</li> <li>Face constructed of high-impact thermoplastic.</li> </ul>	<ul style="list-style-type: none"> <li>Zinc-plated steel strap.</li> <li>Nickel-plated “F” type connector.</li> <li>Threaded on each end.</li> </ul>

Catalog Number	Color	Configuration	3rd Party Compliance UL1863
<b>Combination Coaxial Connector &amp; Telephone Jack</b>			
TPTELTVI	Ivory	F-type COAX Connector with 4 Conductor RJ-11 jack	•
TPTELTVW	White		•
TPTELTV	Brown		•
TPTELTVBK	Black		•
TPTELTVLA	Light Almond		•
26TELTVICC10	Ivory	Same as TPTELTV with	•
26TELTVWCC10	White	one-piece molded plate	•
26TELTVLACC10	Light Almond	Decorator outline.	•



26TELTVCC10

These products listed to UL514, Cover Plates for Flush-Mounted Wiring Devices, CSA Certified.