





GFCI, Surge Receptacles and Style Line® Device Wallplates

| Description | Color | Nylon Standard | Nylon Mid-Size | Material | Metal Catalog Number | |
|---|---|----------------|-----------------|-----------------|----------------------|---|
|  <p>1-Gang, 1-Decorator</p> | Almond | NP26AL | NPJ26AL | Aluminum | ① | |
| | Black | NP26BK | NPJ26BK | Brass | SB26 | |
| | Blue | - | - | Brass Plated | SBP26 | |
| | Brown | NP26 | NPJ26 | Chrome | SCH26 | |
| | Gray | NP26GY | NPJ26GY | S/S 302/304 | SS26 | |
| | Ivory | NP26I | NPJ26I | S/S 430 | SS26L | |
| | Light Almond | NP26LA | NPJ26LA | Steel, Almond | PHPS1AL* | |
| | Office White | NP26OW | NPJ26OW | Steel, Gray | PHPS1G* | |
| | Red | NP26R | NPJ26R | | | |
| | White | NP26W | NPJ26W | | | |
| |  <p>2-Gang, 2-Decorator</p> | Almond | NP262AL | NPJ262AL | Aluminum | ① |
| Black | | NP262BK | NPJ262BK | Brass | SB262 | |
| Brown | | NP262 | NPJ262 | Brass Plated | SBP262 | |
| Gray | | NP262GY | NPJ262GY | Chrome | SCH262 | |
| Ivory | | NP262I | NPJ262I | S/S 302/304 | SS262 | |
| Light Almond | | NP262LA | NPJ262LA | S/S 430 | SS262L | |
| Office White | | NP262OW | NPJ262OW | Steel, Almond | PHPS2AL* | |
| Red | | NP262R | NPJ262R | Steel, Gray | PHPS2G* | |
| White | | NP262W | NPJ262W | | | |
|  <p>3-Gang, 3-Decorator</p> | | Almond | NP263AL | NPJ263AL | Aluminum | ① |
| | | Black | NP263BK | NPJ263BK | Brass | ① |
| | Brown | NP263 | NPJ263 | Brass Plated | SBP263 | |
| | Gray | NP263GY | NPJ263GY | Chrome | ① | |
| | Ivory | NP263I | NPJ263I | S/S 302/304 | SS263 | |
| | Light Almond | NP263LA | NPJ263LA | S/S 430 | - | |
| | Office White | NP263OW | NPJ263OW | Steel, Almond | PHPS3AL* | |
| | Red | NP263R | NPJ263R | | | |
| | White | NP263W | NPJ263W | | | |
| |  <p>4-Gang, 4-Decorator</p> | Almond | NP264AL | NPJ264AL | Aluminum | ① |
| | | Black | NP264BK | NPJ264BK | Brass | ① |
| Brown | | NP264 | NPJ264 | Brass Plated | ① | |
| Gray | | NP264GY | NPJ264GY | Chrome | ① | |
| Ivory | | NP264I | NPJ264I | S/S 302/304 | SS264 | |
| Light Almond | | NP264LA | NPJ264LA | S/S 430 | - | |
| Office White | | NP264OW | NPJ264OW | Steel, Almond | PHPS4AL* | |
| White | | NP264W | NPJ264W | | | |
|  <p>5-Gang, 5-Decorator</p> | | Black | NP265BK | - | Aluminum | ① |
| | | Brown | NP265 | - | Brass | ① |
| | | Gray | NP265GY | - | Brass Plated | ① |
| | Ivory | NP265I | - | Chrome | ① | |
| | Light Almond | NP265LA | - | S/S 302/304 | SS265 | |
| | White | NP265W | - | S/S 430 | - | |
| | | | | Steel, Almond | PHPS5AL* | |
|  <p>6-Gang, 6-Decorator</p> | Black | NP266BK | - | Aluminum | ① | |
| | Brown | NP266 | - | Brass | ① | |
| | Gray | NP266GY | - | Brass Plated | ① | |
| | Ivory | NP266I | - | Chrome | ① | |
| | Light Almond | NP266LA | - | S/S 302/304 | SS266 | |
| | White | NP266W | - | S/S 430 | - | |
| | | | | Steel, Almond | PHPS6AL* | |

Note: All standard and mid-size nylon wallplates feature pre-inserted captive screws for faster assembly, up to 6-gang.
 ① Available as a custom wallplate, see pages N-32 to N-36. Consult custom wallplates section for additional openings and combinations.
 *Powder coat paint finish.

More Style In a Snap

Snap-on wallplates offer a clean, elegant look that can be installed in seconds. Screw the mounting plate onto the device and press the snap-on cover into place. Four snaps securely hold the cover to the subplate.



Decorator, Snap-On, Polycarbonate, Two Piece Construction Wallplates



| Color | 1-Gang, 1-Decorator | 2-Gang, 2-Decorator | 3-Gang, 3-Decorator | 4-Gang, 4-Decorator | 5-Gang, 5-Decorator | 6-Gang, 6-Decorator |
|--------------|------------------------|------------------------|------------------------|------------------------|------------------------|------------------------|
| Ivory | RCW1I | RCW2I | RCW3I | RCW4I | RCW5I | RCW6I |
| Light Almond | RCW1LA | RCW2LA | RCW3LA | RCW4LA | RCW5LA | RCW6LA |
| White | RCW1W | RCW2W | RCW3W | RCW4W | RCW5W | RCW6W |

Decorator, Screw-On, Standard, Nylon Wallplates

| Color | 1-Gang, 1-Decorator | 2-Gang, 2-Decorator | 3-Gang, 3-Decorator | 4-Gang, 4-Decorator | 5-Gang, 5-Decorator | 6-Gang, 6-Decorator |
|--------------|------------------------|------------------------|------------------------|------------------------|------------------------|------------------------|
| Black | NP26BK | NP262BK | NP263BK | NP264BK | NP265BK | NP266BK |
| Brown | NP26 | NP262 | NP263 | NP264 | NP265 | NP266 |
| Gray | NP26GY | NP262GY | NP263GY | NP264GY | NP265GY | NP266GY |
| Ivory | NP26I | NP262I | NP263I | NP264I | NP265I | NP266I |
| Light Almond | NP26LA | NP262LA | NP263LA | NP264LA | NP265LA | NP266LA |
| White | NP26W | NP262W | NP263W | NP264W | NP265W | NP266W |

Decorator, Screw-On, Mid-Size, Nylon Wallplates

| Color | 1-Gang, 1-Decorator | 2-Gang, 2-Decorator | 3-Gang, 3-Decorator | 4-Gang, 4-Decorator | 5-Gang, 5-Decorator | 6-Gang, 6-Decorator |
|--------------|------------------------|------------------------|------------------------|------------------------|------------------------|------------------------|
| Black | NPJ26BK | NPJ262BK | NPJ263BK | NPJ264BK | — | — |
| Brown | NPJ26 | NPJ262 | NPJ263 | NPJ264 | — | — |
| Gray | NPJ26GY | NPJ262GY | NPJ263GY | NPJ264GY | — | — |
| Ivory | NPJ26I | NPJ262I | NPJ263I | NPJ264I | — | — |
| Light Almond | NPJ26LA | NPJ262LA | NPJ263LA | NPJ264LA | — | — |
| White | NPJ26W | NPJ262W | NPJ263W | NPJ264W | — | — |

Decorator, Screw-On, Mid-Size, Metal Wallplates

| Material | 1-Gang, 1-Decorator | 2-Gang, 2-Decorator | 3-Gang, 3-Decorator | 4-Gang, 4-Decorator | 5-Gang, 5-Decorator | 6-Gang, 6-Decorator |
|--------------|------------------------|------------------------|------------------------|------------------------|------------------------|------------------------|
| Brass | SB26 | SB262 | — | — | — | — |
| Brass Plated | SBP26 | SBP262 | SBP263 | — | — | — |
| Chrome | SCH26 | SCH262 | — | — | — | — |
| S/S 302/304 | SS26 | SS262 | SS263 | SS264 | SS265 | SS266 |
| S/S 430 | SS26L | SS262L | — | — | — | — |

Dimensions in Inches (mm)