


6673-10W



UPC Code: 07847751529

Country of Origin: China

Dimmers

Brand Features

Leviton offers many products that will help lower electrical costs and add convenience to everyday living. By simply replacing standard switches with dimmers reduces energy consumption and extends bulb life. IllumaTech Preset Dimmers and Fan Speed Controls feature a low-profile fluid slide bar movement for fine adjustment of light levels or fan speeds that's accompanied by an easy-to-use ON/OFF preset switch. The switch provides quick ON/OFF control without disturbing your favorite pre-selected settings. Most feature a built-in LED locator light, as well. Models are available for incandescent, magnetic or electronic low-voltage, and Mark 10 Powerline dimming-ballast fluorescent lighting, and quiet and standard fan speed control. All Preset models are designed for both single-pole (one-location) and 3-way (multi-location) applications.

Item Description

Decora® Dimmable CFL and Incandescent Sureslide Dimmer, 300W-120VAC CFL and 600W-120VAC Incadescent, 60Hz, single pole and 3-way. Color- White

Technical Information

Product Features

Switch Type: Single-Pole & 3-Way

Style Name: SureSlide

Type: Electro-Mechanical

Preset: Preset

Load Type: CFL and Incandescent

Load Rating: CFL: 300W-120VAC
Incandescent: 600W-120VAC

Voltage: 120 Volt AC 60Hz

Light: Non-Illuminated

Action: Standard ON/OFF

Protection: Radio/TV Filter

Wallplate: Order Separately

Color: White

Standards and Certifications: UL/CSA

Warranty: 5-Year Limited

Features and Benefits

- CFL Dimmer is specifically designed to control a variety of dimmable CFLs
- Auto mode will detect whether a lamp is an incandescent or dimmable CFL, determine low-end dimming capabilities and adjust dimmer range accordingly
- Outperforms incandescent dimmers when controlling dimmable CFLs
- Integrated linear full range slide control for easy, precise operation
- Single-pole (one location) and multi-location lighting control when used with a 3-way switch
- Built-in radio/TV interference filter
- Attractive Decora® designer styling coordinates perfectly with Leviton's complete line Decora® wiring devices
- Compatible with Decora® screwless and Decora® standard designer wallplates
- Slim, compact housing fits easily into a standard wallbox and is suitable for multi-gang installations
- UL Listed and CSA Certified

· Backed by a Limited Five-Year Warranty

SPECIFICATION SUBMITTAL

JOB NAME: <input type="text"/>	CATALOG NUMBERS: <input type="text"/>	
JOB NUMBER: <input type="text"/>	<input type="text"/>	<input type="text"/>

Leviton Manufacturing Co., Inc.

201 North Service Road, Melville, NY 11747

Telephone: 1-800-323-8920 · FAX: 1-800-832-9538 · Tech Line (8:30AM-7:30PM E.S.T. Monday-Friday): 1-800-824-3005

Leviton Manufacturing of Canada, Ltd.

165 Hymus Boulevard, Pointe Claire, Quebec H9R 1E9 · Telephone: 1-800-469-7890 ·

FAX: 1-800-824-3005 · www.leviton.com/canada

Leviton S. de R.L. de C.V.

Lago Tana 43, Mexico DF, Mexico CP 11290 · Tel.: (+52)55-5082-1040 · FAX: (+52)5386-1797 · www.leviton.com.mx

Visit our Website at: www.leviton.com

© 2012 Leviton Manufacturing Co., Inc. All rights reserved. Subject to change without notice.

Leviton has a global presence.

If you would like to know where your local Leviton office is located please go to: www.leviton.com/international/contacts/

