

99W76-S

Watertight and Dust-tight Devices

Item Description

30 Amp, 480 Volt 3-phase, NEMA L16-30, 3P, 4W, Locking Single Outlet, Industrial Grade, Grounding, Wetguard - YELLOW



Technical Information

Electrical Specifications

Amperage: 30 Amp
Voltage: 480 Volt 3-Phase
Pole: 3
Wire: 4
Grounding: Grounding
Dielectric Voltage: Withstands 2000V per UL498
Current Limiting: Full Rated Current
Temperature Rise: Max 30C after 250 cycles OL at 200 percent rated current

Mechanical Specifications

Terminal Accom.: #12 AWG to #8 AWG
Terminal ID: Brass-Hot, Green-Ground, Silver-Neutral
Product ID: Ratings and NEMA I.D. permanently marked on device

Product Features

NEMA: L16-30R
Color: Yellow

Environmental Specifications

Flammability: Rated V-2 per UL 94 (wiring module)
Operating Temperature: -40C to 60C
Enclosure Rating: NEMA 4, 4X, 12 IEC IP66

Standards and Certifications

NEMA: WD-6
ANSI: C-73
UL: 498
CSA: C22.2 No. 42
NOM: 057

Color:  Yellow

UPC Code: 07847751977

Country of Origin: United States - *Eligible for ARRA funded projects



NEMA: L16-30R



Material Specifications

Cover/Lid: Valox PBT
Wiring Module Mounting Cup: Valox PBT
Wiring Module: Nylon
Cover Gasket: Santoprene TPV
Torsion Spring Mechanism: Stainless Steel
Blades/Contacts, Terminal Clamps: Electroless Nickel-coated Brass
Terminal Screws: Electroless Nickel-coated Brass
Mounting & Assembly Screws: Stainless steel, non-magnetic





SPECIFICATION SUBMITTAL

JOB NAME:	CATALOG NUMBERS:	
<input type="text"/>	<input type="text"/>	<input type="text"/>
JOB NUMBER:	<input type="text"/>	<input type="text"/>

Leviton Manufacturing Co., Inc.

201 North Service Road, Melville, NY 11747

Telephone: 1-800-323-8920 · FAX: 1-800-832-9538 · Tech Line (8:30AM-7:30PM E.S.T. Monday-Friday): 1-800-824-3005

Leviton Manufacturing of Canada, Ltd.

165 Hymus Boulevard, Pointe Claire, Quebec H9R 1E9 · Telephone: 1-800-469-7890 ·

FAX: 1-800-824-3005 · www.leviton.com/canada

Leviton S. de R.L. de C.V.

Lago Tana 43, Mexico DF, Mexico CP 11290 · Tel.: (+52)55-5082-1040 · FAX: (+52)5386-1797 · www.leviton.com.mx

Visit our Website at: www.leviton.com

© 2012 Leviton Manufacturing Co., Inc. All rights reserved. Subject to change without notice.



Leviton has a global presence.

If you would like to know where your local Leviton office is located please go to: www.leviton.com/international/contacts/

**Buy American Compliant Logo -- The American Recovery And Reinvestment Act of 2009 ("ARRA") provides federal grants and loans for projects throughout the country. Section 1605 of the Act, named the "Buy American" provision, requires that certain materials and manufactured products used in projects funded by the Act be manufactured in the United States. The appearance of the Recovery Act Logo in relation to a Leviton product is only intended to reflect that such product may be used in an ARRA funded project. It does not mean that such product or Leviton is sponsored or endorsed by, or that Leviton receives funds from, the federal government or the Recovery Accountability and Transparency Board. Nothing in Leviton's use of the logo is intended to suggest anything regarding the requirements for funding under ARRA.*