

# 7210-B



**Color:**  Black

**UPC Code:** 07847783574

**Country of Origin:** United States - *\*Eligible for ARRA funded projects*

**NEMA:** L2-20R



*\*May include one or more globally sourced components.*



## Locking Wiring Devices

### Brand Features

Leviton offers industrial, commercial and residential plugs and connectors for unlimited application settings. Plugs and connectors are provided in a range of ratings from 15 Amps to 60 Amps; the product line includes straight-blade and locking devices in all NEMA configurations, as well as locking devices in non-NEMA configurations. Versions include Hospital Grade, isolated ground, WetGuard, Dustguard, Python, power plugs, corrosion resistant plugs and connectors, power-interrupting devices, midjet devices, and much more.

### Item Description

20 Amp, 250-Volt, NEMA L2-20, 2-Pole, 2-Wire, Single Receptacle - BLACK

### Technical Information

#### Electrical Specifications

**Grounding:** Non-Grounding

**Amperage:** 20 Amp

**Voltage:** 250 Volt

**NEMA:** L2-20R

**Pole:** 2

**Wire:** 2

**Dielectric Voltage:** Withstands 2000V per UL498

**Current Interrupting:** Certified for current interrupting at full rated current

**Temperature Rise:** Max 30C after 250 cycles OL at 200 percent rated current

#### Environmental Specifications

**Flammability:** UL94V-2

**Operating Temperature:** -40deg.C to 75deg.C (-40deg.F to 167deg.F)

#### Material Specifications

**Cover Material:** Nylon

**Base Material:** RTP

**Contact - Spring Value:** 0.041inch thick Brass

**Clamp Nuts:** Brass

**Ground Contacts:** Brass

**Ground Shunt:** Brass

**Terminal Screws:** Brass 10-32

**Grounding Screw:** Bronze

**Mounting Screws:** Zinc-Plated Steel 8-32

**Color:** Black

#### Mechanical Specifications

**Terminal Accom.:** 16-8 AWG


**Terminal ID:** X,Y,Z, White, Green

**Product ID:** Ratings are permanently marked on device

#### Product Features

**NEMA:** L2-20R

**Color:** Black



**L2-20R**

**SPECIFICATION SUBMITTAL**

JOB NAME:		CATALOG NUMBERS:	
<input type="text"/>		<input type="text"/>	<input type="text"/>
JOB NUMBER:	<input type="text"/>	<input type="text"/>	<input type="text"/>

**Leviton Manufacturing Co., Inc.**  
 201 North Service Road, Melville, NY 11747  
 Telephone: 1-800-323-8920 · FAX: 1-800-832-9538 · Tech Line (8:30AM-7:30PM E.S.T. Monday-Friday): 1-800-824-3005

**Leviton Manufacturing of Canada, Ltd.**  
 165 Hymus Boulevard, Pointe Claire, Quebec H9R 1E9 · Telephone: 1-800-469-7890 ·  
 FAX: 1-800-824-3005 · [www.leviton.com/canada](http://www.leviton.com/canada)

**Leviton S. de R.L. de C.V.**  
 Lago Tana 43, Mexico DF, Mexico CP 11290 · Tel.: (+52)55-5082-1040 · FAX: (+52)5386-1797 · [www.leviton.com.mx](http://www.leviton.com.mx)

Visit our Website at: [www.leviton.com](http://www.leviton.com)  
 © 2012-2013 Leviton Manufacturing Co., Inc. All rights reserved. Subject to change without notice.

**Leviton has a global presence.**  
 If you would like to know where your local Leviton office is located please go to: [www.leviton.com/international/contacts/](http://www.leviton.com/international/contacts/)

*\*Buy American Compliant Logo -- The American Recovery And Reinvestment Act of 2009 ("ARRA") provides federal grants and loans for projects throughout the country. Section 1605 of the Act, named the "Buy American" provision, requires that certain materials and manufactured products used in projects funded by the Act be manufactured in the United States. The appearance of the Recovery Act Logo in relation to a Leviton product is only intended to reflect that such product may be used in an ARRA funded project. It does not mean that such product or Leviton is sponsored or endorsed by, or that Leviton receives funds from, the federal government or the Recovery Accountability and Transparency Board. Nothing in Leviton's use of the logo is intended to suggest anything regarding the requirements for funding under ARRA.*

