

T5632-W



UPC Code: 07847768386

Country of Origin: China

USB Charger/Duplex Tamper-Resistant Receptacle

Brand Features

The Leviton USB Charger/Tamper-Resistant Duplex Receptacle offers two high-powered USB Ports with 3.6A of charging power and two 15A or 20A/125V Tamper-Resistant Receptacles. It has the capability to charge two USB powered electronic devices utilizing its two USB Ports, leaving the two Tamper-Resistant Receptacles free for other uses. The Leviton USB Charger/Tamper-Resistant Duplex Receptacle is designed to charge tablets, smart and mobile phones, gaming devices, e-readers, digital cameras and a host of other electronic devices.

Item Description

Combination Duplex Receptacle and USB Charger. 15 Amp, 125 Volt, Decora Tamper-Resistant Receptacle, NEMA 5-15R. 3.6 Amps, 5VDC, 2.0 Type A USB Chargers. Grounding, Side Wired & Back Wired - White.

Technical Information

Electrical Specifications

Receptacle Amperage: 15 Amp

Receptacle Voltage: 125V AC

Ratings: 15A-125V

Horsepower Rating: 15A-1/2 HP

Grounding: Grounding

Mechanical Specifications

Torque Range: 12-14 inch pounds

Terminal Accom.: 14-12 AWG

Product ID: Stamped on Strap

Termination: Back & Side

Terminal ID: Brass-Hot Black-Hot White-Neutral Green-Gnd

Environmental Specifications

Operating Temperature: -10C to 40C

Operating Temperature: -10C to 40C

Flammability: Rated V-0 per UL94

Product Features

Color: White

Material Specifications

Cover Material: Thermoplastic

Strap Material: Steel

Color: White

Body Material: Thermoplastic

Standards and Certifications

Warranty: 5 Year Limited

Listed: cCSAus

Listed: cCSAus

NOM: 057

FCC Part 15: Class B for Residential Compliance

Features and Benefits

- Perfect for use in residential applications such as kitchens, bedrooms and home offices and in commercial applications such as hotels, airports, restaurants and cafes, salons, office cubicles and college dorm rooms
- Smart chip recognizes and optimizes the charging requirements of individual devices
- USB Ports are positioned vertically providing more space for maneuvering and reducing stress on USB cables
- Compatible with USB 2.0 devices
- Fits in a standard wallbox, is compatible with standard wallplates and can be multi-ganged with other devices
- Easy to install. Can replace existing outlets

SPECIFICATION SUBMITTAL

JOB NAME: <input type="text"/>	CATALOG NUMBERS: <input type="text"/>	
JOB NUMBER: <input type="text"/>	<input type="text"/>	<input type="text"/>

Leviton Manufacturing Co., Inc.
201 North Service Road, Melville, NY 11747
Telephone: 1-800-323-8920 · FAX: 1-800-832-9538 · Tech Line (8:30AM-7:30PM E.S.T. Monday-Friday): 1-800-824-3005

Leviton Manufacturing of Canada, Ltd.
165 Hymus Boulevard, Pointe Claire, Quebec H9R 1E9 · Telephone: 1-800-469-7890 ·
FAX: 1-800-824-3005 · www.leviton.com/canada

Leviton S. de R.L. de C.V.
Lago Tana 43, Mexico DF, Mexico CP 11290 · Tel.: (+52)55-5082-1040 · FAX: (+52)5386-1797 · www.leviton.com.mx

Visit our Website at: www.leviton.com
© 2012-2014 Leviton Manufacturing Co., Inc. All rights reserved. Subject to change without notice.

Leviton has a global presence.
If you would like to know where your local Leviton office is located please go to: www.leviton.com/international/contacts/

