

66W81

66W81



Color:  Yellow

Where To Buy

Market Channel

enter your zip code

[Technical Information](#) [Support](#) [Related Products](#) [Videos](#)

Technical Information

[TOP](#)

UPC Code: 07847751925
Country Of Origin: United States
* Eligible for ARRA funded projects

NEMA:
L21-20P



[*Disclaimer...](#)

Product Lists

[Add to Product List](#)

[View Product List](#)

Quantity:

Electrical Specifications

Amperage: 20 Amp
Voltage: 120/208 VAC 3-phase WYE
Pole: 4
Wire: 5
Grounding: Grounding
Dielectric Voltage: Withstands 2000V per UL498
Current Limiting: Full Rated Current
Temperature Rise: Max 30C after 250 cycles OL at 200 percent rated current

Environmental Specifications

Flammability: Rated V-2 per UL 94 (wiring module)
Operating Temperature: -40C to 60C
Enclosure Rating: NEMA 4, 4X, 12 IEC IP66

Material Specifications

Cover/Lid: Valox PBT
Wiring Module Mounting Cup: Valox PBT
Wiring Module: Nylon
Cover Gasket: Santoprene TPV
Torsion Spring Mechanism (Flip Lids): Stainless Steel
Blades/Contacts, Terminal Clamps: Electroless Nickel-coated Brass
Terminal Screws: Electroless Nickel-coated Brass
Mounting & Assembly Screws: Stainless steel, non-magnetic

Mechanical Specifications

Terminal Accom.: #16 AWG to #10 AWG
Product ID: Ratings and NEMA I.D. permanently marked on device

Product Features

NEMA: L21-20P
Color: Yellow

Standards and Certifications

NEMA: WD-6
ANSI: C-73
UL: 498
CSA: C22.2 No. 42
NOM: 057
Warranty: Lifetime Limited

[Product Brochure](#)

[Dimensional Data](#)

[Instruction Sheet](#)

[Instruction Sheet - Spanish](#)

Related Products



76W81-C

20 Amp, 120/208 Volt, 3 Phase WYE, NEMA L21-20, 4P, 5W, Locking Connector for Single Inlet, Industrial...
[More](#)



FDBX1-Y

FD Box, Single-Gang, 26.0 Cubic Inch Capacity, 1" unthreaded conduit openings with reducers for 3/4" a...
[More](#)



FDBX2-Y

FD Box, Two-Gang, 67.3 Cubic Inch Capacity, 1" unthreaded conduit openings with reducers for 3/4" and ...
[More](#)



FD Box, 1... Inch Capa... openings...
[More](#)

Videos

Wetguard

Leviton Wetguard® Watertight Wiring Devices



Wetguard

ABOUT LEVITON

Leviton is the smart choice, delivering the most comprehensive range of solutions to meet the needs of today's residential, commercial and industrial customers in more than 90 countries across the globe. From simple switches and receptacles, to networking systems and smart home automation, Leviton exceeds market needs by delivering innovative products to create sustainable, intelligent environments through its electrical wiring devices, network and data center connectivity solutions, LED lighting and lighting energy management systems, and security and automation applications. For Leviton, it is clear the FUTURE IS ON.



PRODUCTS

- Connected Home
- Electric Vehicle Charging
- Electrical Wiring Devices
- GFCIs and AFCIs
- Lighting Controls
- Network Solutions
- Security & Automation
- Submetering
- Surge Protective Devices
- Temporary Power

SOLUTIONS

- Applications
- Brands
- Business
- Contech Lighting
- Intense Lighting
- Energy Management
- Government
- Home Solutions
- Industrial
- JCC Lighting Products
- Security & Automation

SUPPORT

- Contact Us
- Cross Reference
- Discussions
- Documents & Resources
- ez-Biz
- ez-Learn
- Knowledgebase
- Leviton Warranties
- Mobile Apps
- Product Support
- Quality Concerns