


110-Style Connector Clips

APPLICATION

Leviton 110-Style Connector Clips are used with a 110 wiring block to provide a gas-tight IDC connection. Connector clips are available in three pair-count sizes: C-3 for use with 3-pair cables, C-4 for use with 4-pair cables, and C-5 for use with 25-pair cables.



SPECIFICATION

110 connector clips shall support termination for voice, security, and Category 5e data applications, including high megabit and shared-sheath applications when used with Power Sum-rated cabling. Clips shall be Category 5e compliant, UL listed and ANSI/TIA-568-C.2 compliant. They shall be made of fire-retardant UL 94V-0 plastic with solder-plated insulation displacement connectors, and must securely seat wires on 110 wiring bases, providing a gas-tight IDC connection that can withstand 200 re-terminations.

FEATURES

- Available in three pair-count sizes: C-3, C-4, and C-5
- Connector clips can withstand 200 re-terminations

DESIGN CONSIDERATIONS

- Seat the connector blocks on the 110-wiring-base index strip with a 5-pair spring-loaded termination tool

STANDARDS COMPLIANCE

ANSI/TIA-568-C.2
ANSI/TIA-1096-A (formerly FCC Part 68)
cULus Listed

PHYSICAL SPECIFICATIONS

Dimensions: See page two
Materials: Made of fire-retardant plastic rated UL 94V-0 with solder-plated IDCs

WARRANTY INFORMATION

For a copy of Leviton product warranties, visit www.leviton.com/warranty.

Leviton Network Solutions

2222 - 222nd St. SE
Bothell, WA 98021-4416

tel 1-800-824-3005
tel +1-425-486-2222
appeng@leviton.com
www.leviton.com

Asia / Pacific

T +1.631.812.6228
E infoasean@leviton.com

Europe

T +33.6.8869.1380
E infoeurope@leviton.com

Canada

T +1.514.954.1840
E pcservice@leviton.com

India / SAARC

T +971.4.886.4722
E infoindia@leviton.com

Caribbean

T +1.954.593.1896
E infocaribbean@leviton.com

Mexico

T +52.55.5082.1040
E lsamarketing@leviton.com

China

T +852.2774.9876
E infochina@leviton.com

Middle East & Africa

T +971.4.886.4722
E lmeinfo@leviton.com

Colombia

T +57.1.743.6045
E infocolombia@leviton.com

South Korea


T +82.2.3273.9963
E infokorea@leviton.com

ELECTRONIC FILES


For CAD files, typical specs, or technical drawings (.DXF, .DWG), visit www.leviton.com.

4910x-IDC, 49104-150


C-3 Connector Clip



C-4 Connector Clip



C-5 Connector Clip



PART NUMBERS

Description	Part No.
C-3 110-Style Connector Clip (bag of 10)	49103-IDC
C-4 110-Style Connector Clip (bag of 10)	49104-IDC
C-4 110-Style Connector Clip (bag of 50)	49104-150
C-5 110-Style Connector Clip (bag of 10)	49105-IDC



Leviton Network Solutions
 2222 - 222nd St. SE
 Bothell, WA 98021-4416

Asia / Pacific
 T +1.631.812.6228
 E infoasean@leviton.com

Canada
 T +1.514.954.1840
 E pcservice@leviton.com

Caribbean
 T +1.954.593.1896
 E infocaribbean@leviton.com

China
 T +852.2774.9876
 E infochina@leviton.com

Colombia
 T +57.1.743.6045
 E infocolombia@leviton.com

tel 1-800-824-3005
 tel +1-425-486-2222
appeng@leviton.com
www.leviton.com

Europe
 T +33.6.8869.1380
 E infoeurope@leviton.com

India / SAARC
 T +971.4.886.4722
 E infoindia@leviton.com

Mexico
 T +52.55.5082.1040
 E lsamarketing@leviton.com

Middle East & Africa
 T +971.4.886.4722
 E lmeinfo@leviton.com

South Korea
 T +82.2.3273.9963
 E infokorea@leviton.com