

8590-RBI


Description

NO IMAGE FOUND

Switch-Rated SmartLockPRO GFCI, 20 Amp 125V Feed-Through, Blank Face, No Indicator Light, Black and Red Test and Reset Buttons. - IVORY

Product Features

Color: Ivory



- Grounding: GFCI Ground Fault
- Feature: Switch Rated Blank Face
- Amperage: 20 Amp
- Voltage: 125 Volt
- Termination: Back & Side 20A Feed-Thru
- Face Material: Thermoplastic Nylon
- Body Material: Thermoplastic Nylon
- Strap Material: Steel
- Color: Ivory

Standards and Certifications: UL/CSA/NOM

Warranty: 2 Year Limited

Features and Benefits

- 20A Switch Rated Test/Reset Buttons
- Automatically test the GFCI every time the RESET button is pushed in. The GFCI will not reset if the GFCI circuit in not functioning properly.
- Trip threshold meets or exceeds UL943 GFCI Safety Standards
- Improved immunity to high-frequency noise reduces nuisance tripping
- Advanced electronics design provides superior resistance to electrical surges and over-voltages
- Silver alloy contacts

AC Horsepower Ratings	
At Rated Voltage	1-1/2 HP

Environmental Specifications	
Flammability	Rated V-2 per UL94
Operating Temperature	-35C to 65C

Mechanical Specifications	
Terminal ID	Brass-Hot, Green-Ground, Silver-Neutral
Terminal Accom.	14-12 AWG
Product ID	Ratings permanently marked on device

Electrical Specifications	
Dielectric Voltage	Withstands 1500V per UL498
Current Limiting	10kA
Temperature Rise	Max 30C after 50 cycles OL at 150 percent rated current

Material Specifications	
Face Material	Thermoplastic Nylon
Body Material	Thermoplastic Nylon
Terminal Screws	Brass 10-32
Grounding Screw	Brass 8-32 Back Wired
Yoke	Zinc-Plated Steel

Standards and Certifications	
NEMA	WD-6
ANSI	C-73
UL 498	File E13399
CSA C22.2 No. 42	File LR-57811
NOM	057

SPECIFICATION SUBMITTAL

JOB NAME: <input type="text"/>	CATALOG NUMBERS: <input type="text"/>	
JOB NUMBER: <input type="text"/>	<input type="text"/>	<input type="text"/>

Leviton Manufacturing Co., Inc.

201 North Service Road, Melville, NY 11747

Telephone: 1-800-323-8920 · FAX: 1-800-832-9538 · Tech Line (8:30AM-7:30PM E.S.T. Monday-Friday): 1-800-824-3005

Leviton Manufacturing of Canada, Ltd.

165 Hymus Boulevard, Pointe Claire, Quebec H9R 1E9 · Telephone: 1-800-469-7890 · FAX: 1-800-824-3005

Leviton S. de R.L. de C.V.

Lago Tana 43, Mexico DF, Mexico CP 11290 · Tel.: (+52)55-5082-1040 · FAX: (+52)5386-1797 · www.leviton.com.mx



Visit our Website at: www.leviton.com

© 2007-2009 Leviton Manufacturing Co., Inc. All rights reserved. Subject to change without notice.