



By using this site, you consent to the use of cookies for purposes including advertising and analytics. [Learn More](#)



[Home](#) [Products](#) [Electrical Wiring Devices](#) [Watertight Wiring Devices](#) [Wetguard® Watertight](#) [FD Boxes](#) [FDBX3-Y](#)

[EMAIL](#) | [PRINT](#) | [PDF](#)

FDBX3-Y



Color:  Yellow

UPC Code: 07847751857
Country Of Origin: United States
* Eligible for ARRA funded projects



[*Disclaimer...](#)

Choose a Color



Gray



Yellow

Product Lists

[Add to Product List](#)

[View Product List](#)

Quantity:

FDBX3-Y

Brand Features

Leviton's Wetguard line of industrial watertight wiring devices are the most versatile, well-engineered watertight devices on the market. They meet IP67 and NEMA ratings for water ingress protection, and offer many significant advantages over competitive brands. Standard color options include yellow and gray with black available upon special request.

Item Description

FD Box, Three-Gang, 109.1 Cubic Inch Capacity, 1" unthreaded conduit openings with reducers for 3/4" and 1/2" conduit, includes plugs for unused openings and stainless steel device mounting plates with ground wire, industrial grade - YELLOW

Where To Buy

enter your zip code

[Technical Information](#) [Support](#) [Related Products](#) [Videos](#)

Technical Information

[TOP](#)

Environmental Requirements

Operating Temperature: -20°F (-29°C) to +140°F(+60°C)

Environmental Specifications

Enclosure Rating: NEMA 4, 4X, 12 IEC IP66

Material Specifications

Box: Rigid PVC
Reducers/Plugs: Rigid PVC
Frame (2-and 3-gang): Valox PBT
Gasket (2-and3-gang): Santoprene TPV
Threaded Inserts: Brass
Mounting Plate: Stainless Steel
Grounding Wire: Green #12AWG Stranded Copper, 8" Long

Mechanical Specifications

Box Volume: 109.1 cu in/1788 cu cm

Product Features

Color: Yellow

Standards and Certifications

cULus: Listed

Support

[TOP](#)

[Product Brochure](#)

[Dimensional Data](#)

[Instruction Sheet](#)

Related Products

TOP



COVER-S

Wetguard Watertight Toggle Switch Cover, IP66, NEMA 4 & 4X, For use with all 15A-40A Toggle Switches i...
[More](#)



FDBX3-GY

FD Box, Three-Gang, 109.1 Cubic Inch Capacity, 1" unthreaded conduit openings with reducers for 3/4" a...
[More](#)



WP459

Wetguard Receptacle Blank Plate and Gasket - YELLOW
[More](#)

Videos

TOP

Wetguard

Leviton Wetguard® Watertight Wiring Devices



Wetguard

ABOUT LEVITON

Leviton is the smart choice, delivering the most comprehensive range of solutions to meet the needs of today's residential, commercial and industrial customers in more than 90 countries across the globe. From simple switches and receptacles, to networking systems and smart home automation, Leviton exceeds market needs by delivering innovative products to create sustainable, intelligent environments through its electrical wiring devices, network and data center connectivity solutions, LED lighting and lighting energy management systems, and security and automation applications. For Leviton, it is clear the FUTURE IS ON.



PRODUCTS

Connected Home
Electric Vehicle Charging
Electrical Wiring Devices
GFCIs and AFCIs
Lighting Controls
Network Solutions
Security & Automation
Submetering
Surge Protective Devices
Temporary Power

SOLUTIONS

Applications
Brands
Business
Contech Lighting
Intense Lighting
Energy Management
Government
Home Solutions
Industrial
JCC Lighting Products
Security & Automation

SUPPORT

Contact Us
Cross Reference
Discussions
Documents & Resources
ez-Biz
ez-Learn
Knowledgebase
Leviton Warranties
Mobile Apps
Product Support
Quality Concerns