


OPB15-DAW



Color: White

UPC Code: 07847750871
Country Of Origin: United States
* Eligible for ARRA funded projects



[*Disclaimer...](#)

Product Lists

[Add to Product List](#)

[View Product List](#)

Quantity:

OPB15-DAW

Brand Features

The OPB15 Power Base is a unique, patent-pending, 15 Amp power pack for low-voltage occupancy sensors packaged in a housing that forms the mounting base of these products. This allows for installations where only line-voltage circuitry is available while providing the full-line of Leviton low-voltage ceiling sensors to meet every application. The OPB15 Power Base provides all of the same features as the standard OSP Power Pack Series with a full rated 15 amp, zero cross relay with 24 VDC supply. The Power Base Adapter converts any Leviton low voltage ceiling occupancy sensor to a self-contained, line voltage unit, with 15 Amp, 120-277V load capacity.

Item Description

The Power Base™ Adapter converts any Leviton low voltage ceiling occupancy sensor to a self-contained, line voltage unit, with 15Amp, 120/277V load capacity, Made in USA, Title 24 Compliant, ASHRAE 90.1 Compliant

Where To Buy

enter your zip code

[Technical Information](#) [Features and Benefits](#) [Support](#)

Technical Information

[TOP](#)

Electrical Specifications

Input Voltage: 120/277 Volt AC
60Hz

Control Input: 5mA 24VDC

Load Rating: 15 Amp FL/INC

Power Supply Output: 40mA
24VDC

Environmental Specifications

Operating Temperature: 32F to
104F 0C to 40C

Operating Humidity: 0 Pct to 90 Pct
Relative, Non-Condensing

Material Specifications

Color: White

Housing Material: High Impact
Plastic

Contact Material: Silver Alloy

Wire Leads: 14AWG 6 Inch Power
22AWG 7 Inch Control

Product Features

Device Type: Power Base

Load Rating: 15 Amp FL/INC

Input Voltage: 120/277 Volt AC
60Hz

Standards and Certifications

CUL/US: Listed 9034

CSA: Certified

ANCE: Compliant

NOM: 057

FCC: Compliant

ASHRAE: Standard 90.1 Compliant

California Title 24: CEC Listed

Control Input: 5mA 24VDC
Power Supply Output: 40mA
24VDC
Color: White
Standards and Certifications:
CUL/US
Warranty: 5-Year Limited
Domestic Content: Made in USA

Features and Benefits

TOP

- Converts any Leviton low-voltage ceiling sensor to line-voltage (Patent-Pending)
- Mounts to standard 2.125 inch deep X 4 inch octagon or 2.125 inch deep X 4 inch foursquare electrical boxes (foursquare box requires a two-gang mud ring)
- Simple installation
- Ideal for retrofit or new construction applications
- Zero crossing circuitry provides increased durability

Support

TOP

[Instruction Sheet - Power Base](#)

[Instruction Sheet - Spanish](#)

[Instruction Sheet - French](#)

[Application Note - Energy Policy Act of 2005](#)

[Application Note - Changes in Title 24](#)

[Technical Article - Leviton Product Solutions and High Inrush LEDs](#)

[Application Note - IECC VS ASHRAE 90.1-2001](#)

[Application Note - IRS AND ENERGY MANAGEMENT OFFICIAL STATEMENT](#)

[Application Note - How Leviton is Ready to Help You Achieve Leed Points](#)

[Application Note - ADA and FDA Ultrasonic and MultiTechnology](#)

[Specification \(AIA\) - Occupancy Sensors](#)

[Compliance Letter - NAFTA](#)

[Product Specification and Data Sheet](#)

Leviton is the smart choice, delivering the most comprehensive range of solutions to meet the needs of today's residential, commercial and industrial customers in more than 90 countries across the globe. From simple switches and receptacles, to networking systems and smart home automation, Leviton exceeds market needs by delivering innovative products to create sustainable, intelligent environments through its electrical wiring devices, network and data center connectivity solutions, LED lighting and lighting energy management systems, and security and automation applications. For Leviton, it is clear the FUTURE IS ON.



PRODUCTS

- Connected Home
- Electric Vehicle Charging
- Electrical Wiring Devices
- GFCIs and AFCIs
- Lighting Controls
- Network Solutions
- Security & Automation
- Submetering
- Surge Protective Devices
- Temporary Power

SOLUTIONS

- Applications
- Brands
- Business
- Contech Lighting
- Intense Lighting
- Energy Management
- Government
- Home Solutions
- Industrial
- JCC Lighting Products
- Security & Automation

SUPPORT

- Contact Us
- Cross Reference
- Discussions
- Documents & Resources
- ez-Biz
- ez-Learn
- Knowledgebase
- Leviton Warranties
- Mobile Apps
- Product Support
- Quality Concerns