


## TSL06-1LW



Color:



White

UPC Code: 07847777172

Country Of Origin: China

## TSL06-1LW

### Brand Features

Leviton Toggle Slide Universal Dimmers provide smooth, slide-action, full-range dimming for incandescent, dimmable LEDs and dimmable CFL loads. They combine a toggle switch with a full-range slide bar for precise lighting control. For a traditional home, the classic style of Toggle Slide Controls offers the ideal way to upgrade the functionality of devices without compromising the character of the décor.

### Item Description

Universal Dimmable LED, CFL, Incandescent and Halogen Toggle-Slide Dimmer, 600W-120VAC Incandescent, 300W-120VAC 60Hz, Single Pole and 3-Way - White

### Technical Information

#### Product Features

**Phase Control:** Forward phase control

**Action:** Toggle Switch for ON/OFF, slide bar for lighting level control

**Warranty:** 5-Year Limited

**Preset:** Slide bar preserves desired lighting level

**Color:** White

**Switch Type:** Single-Pole & 3-Way

**Load Type:** Incandescent, Halogen, Dimmable LED, Dimmable CFL

**Available Colors:** White, Ivory, Light Almond

**Wallplate:** Order Separately

**Type:** Electro-Mechanical

**tsa\_control:** Preset Slide

**Locator Light:** Green locator light that can be disabled

**Load Rating:** 600W Incandescent and Halogen, 300W LED and CFL

**Voltage:** 120 VAC

**Style Name:** Toggle Slide

**Standards and Certifications:** cCSAus, NOM

**Protection:** Radio/TV Filter

### Features and Benefits

- Designed for optimal control of dimmable LED and CFL lamps. Also compatible with Incandescent and Halogen lamps.
- Microprocessor control offers flexibility to fine-tune for best performance with LED and CFL's
- Setting available for ensuring start up for CFL lamps
- Wider dimming range for LED and CFL lamps than conventional incandescent dimmers
- Programming feature allows users to modify the dimming range to optimize low light level performance when required
- Toggle switch with built-in locator light can be disabled
- Integrated linear full-range slide control for easy, precise operation
- Separate ON/OFF toggle switch that preserves the selected setting
- Provides single pole (one location) or 3-way (two location) control when paired with a 3-way switch
- Slim, compact housing fits easily into a standard wallbox
- Suitable for multi-gang installations
- No removal of fins required for multi-gang installations
- Available in White, Ivory and Light Almond
- Built-in radio/TV interference filter

### SPECIFICATION SUBMITTAL

JOB NAME: <input type="text"/>	CATALOG NUMBERS: <input type="text"/>	
JOB NUMBER: <input type="text"/>	<input type="text"/>	<input type="text"/>

#### Leviton Manufacturing Co., Inc.

201 North Service Road, Melville, NY 11747

Teléfono: +1-800-323-8920 · FAX: +1-800-832-9538 · Tech Line (8:30AM-7:30PM E.S.T. Monday-Friday): +1-800-824-3005

#### Leviton Manufacturing of Canada, Ltd.

165 Hymus Boulevard, Pointe Claire, Quebec H9R 1E9 · Telephone: +1-800-469-7890 ·

FAX: +1-800-824-3005 · [www.leviton.com/canada](http://www.leviton.com/canada)

#### Leviton S. de R.L. de C.V.

Lago Tana 43, Mexico DF, Mexico CP 11290 · Tel.: (+52)55-5082-1040 · FAX: (+52)5386-

1797 · [www.leviton.com.mx](http://www.leviton.com.mx)

Visit our Website at: [www.leviton.com](http://www.leviton.com)

© 2012 Leviton Manufacturing Co., Inc. Todos los derechos reservados. Subject to change without notice.

#### Leviton has a global presence.

If you would like to know where your local Leviton office is located please go to:

[www.leviton.com/international/contacts/](http://www.leviton.com/international/contacts/)

