

8319-CT



UPC Code: 07847779912
Country Of Origin: United States
* Eligible for ARRA funded projects

8319-CT

Brand Features

The Leviton line of Straight Blade Plugs and Connectors includes: Black & White® Industrial Grade devices that resist impact, corrosion and chemicals; Wetguard® for water or moisture resistance; Dustgard® for dust and dirt; Python™, with an innovative interlocking design; rugged nylon flanged and outlets; and integrated inlets and outlets with weather resistant covers.

Item Description

20 Amp, 125 Volt, NEMA 5-20R, 2P, 3W, Connector, Straight Blade, Hospital Grade, Grounding - Transparent

Where To Buy

Market Channel

enter your zip code

[Technical Information](#) [Support](#) [Related Products](#)

NEMA:
5-20R



*Disclaimer...

Choose a Color



Black-White



Transparent

Product Lists

[Add to Product List](#)

[View Product List](#)

Quantity:

Technical Information

[TOP](#)

Electrical Specifications

Grounding: Grounding
Amperage: 20 Amp
Voltage: 125 Volt
Pole: 2
Wire: 3
Temperature Rise: Max 30C after 250 cycles OL at 200 percent rated current
Dielectric Voltage: Withstands 2000V per UL498
Current Interrupting: Certified for current interrupting at full rated current

Environmental Specifications

Flammability: Rated V-2 per UL94
Operating Temperature: -40C to 60C

Material Specifications

Body Material: Super Tough Nylon
Back Cover: Thermoplastic
Wire Module: Nylon
Cord-Clamp: Nylon
Clamp Insert: Nylon
Blades/Contacts: Solid Brass
Terminal Screws: Brass
Assembly Screws: Steel, Zinc Plated
Color: Transparent

Mechanical Specifications

Terminal ID: Brass-Hot, Green-Ground, White-Neutral
Terminal Accom.: 18-10 AWG
Product ID: Ratings and NEMA I.D. permanently marked on device
Cord Range: .245 - .700

Product Features

NEMA: 5-20R
Color: Transparent

Standards and Certifications

NEMA: WD-6
ANSI: C-73
UL 498: File E13399
UL Fed Spec WC-596: File E13393
CSA C22.2 No. 42: File LR-406
NOM: 057
Warranty: Lifetime Warranty

Dimensional Data

Wiring Diagram

Related Products



8315-CT

20 Amp, 125 Volt, NEMA 5-20P, 2P, 3W, Plug, Straight Blade, Hospital Grade, Grounding - Transparent



8319-C

20 Amp, 125 Volt, NEMA 5-20R, 2P, 3W, Connector, Straight Blade, Hospital Grade, Grounding - Black-Whi...

More

ABOUT LEVITON

Leviton is the smart choice, delivering the most comprehensive range of solutions to meet the needs of today's residential, commercial and industrial customers in more than 90 countries across the globe. From simple switches and receptacles, to networking systems and smart home automation, Leviton exceeds market needs by delivering innovative products to create sustainable, intelligent environments through its electrical wiring devices, network and data center connectivity solutions, LED lighting and lighting energy management systems, and security and automation applications. For Leviton, it is clear the FUTURE IS ON.



PRODUCTS

- Connected Home
- Electric Vehicle Charging
- Electrical Wiring Devices
- GFCIs and AFCIs
- Lighting Controls
- Network Solutions
- Security & Automation
- Submetering
- Surge Protective Devices
- Temporary Power

SOLUTIONS

- Applications
- Brands
- Business
- Contech Lighting
- Intense Lighting
- Energy Management
- Government
- Home Solutions
- Industrial
- JCC Lighting Products
- Security & Automation

SUPPORT

- Contact Us
- Cross Reference
- Discussions
- Documents & Resources
- ez-Biz
- ez-Learn
- Knowledgebase
- Leviton Warranties
- Mobile Apps
- Product Support
- Quality Concerns