

## M1636-I



Color:  Ivory

UPC Code: 07847736423  
Country Of Origin: Mexico


\*Eligible for ARRA funded projects > \$7,443,000

**NEMA:**  
5-20R



[\\*Disclaimer...](#)

Choose a Color



## M1636-I

### Brand Features

The Lev-Lok® Modular Wiring Device System is engineered for fast and easy installation. These devices employ a simple twist and lock wiring module that ensures a safe, reliable connection while at the same time providing for extremely fast and easy installation. Lev-Lok brand wiring devices address the reliability and performance concerns of specification engineers without sacrificing the contractor's need for fast, easy installation. Available in extra heavy duty hospital and industrial grades, and heavy duty commercial grade platforms.

### Item Description

20 Amp, 125 Volt, NEMA 5-20R, 2P, 3W, Lev-Lok® Duplex Receptacle, Decora Plus, Straight Blade, Commercial Grade, Self-Grounding, Modular Terminals, Steel Strap - IVORY

### Mating Lev-Lok Wiring Module Required for Use

### Where To Buy

Market Channel

enter your zip code

[Technical Information](#) [Support](#) [Related Products](#) [Videos](#)

## Technical Information

TOP

### AC Horsepower Ratings

**Horsepower Rating:** 1 HP

### Electrical Specifications

**Amperage:** 20 Amp

**Voltage:** 125 Volt

**Pole:** 2

**Wire:** 3

**Grounding:** Self-Grounding

**Dielectric Voltage:** Withstands 2000V per UL498

**Maximum Working Voltage:** 125V as rated

**Current Interrupting:** Certified for current interrupting at full rated current

**Temperature Rise:** Max 30C after 250 cycles OL at 200 percent rated current

### Environmental Specifications

**Flammability:** Rated V-2 per UL94

**Operating Temperature:** -40C to 60C

### Material Specifications

**Cover Material:** Nylon

**Base Material:** Nylon

### Mechanical Specifications

**Product ID:** Ratings are permanently marked on device

**Termination:** Modular Terminals

### Product Features

**Color:** Ivory

**NEMA:** 5-20R

### Standards and Certifications

**NEMA:** WD-1 & WD-6

**cULus:** Listed

**NOM Certified:** 057

**ANSI:** C-73

**Warranty:** 10 Year Limited

## Product Lists

[Add to Product List](#)

[View Product List](#)

Quantity:

**Mounting Strap:** Galvanized Steel with Riveted Ground Contacts

**Ground Clips:** Brass

**Line Contacts:** 0.040" Thick Solid Brass

**Locking Pins:** Solid Brass

**Mounting Screws:** Triple Combination Head, Steel

## Support

[TOP](#)

[Product Brochure](#)

[Dimensional Data](#)

[Instruction Sheet](#)

[Wiring Diagram](#)

## Related Products

[TOP](#)



**MSTWL-A**

20 Amp, 125 Volt, 2P, 3W, Right Angle Wiring Module for Lev-Lok Receptacles, 6" THHN #12 AWG Stranded ...  
[More](#)



**84401-40**

1-Gang Decora/GFCI Device Decora Wallplate/Faceplate, Standard Size, 302 Stainless Steel, Device Mount...  
[More](#)



**LVLOK-TST**

Circuit Analyzer for Lev-Lok Receptacle Modules (MSTWL), cCSAus Listed  
[More](#)



20 Amp, 125 Volt, 2P, 3W, Right Angle Wiring Module for Lev-Lok Receptacles, 6" THHN #12 AWG Stranded ...  
[More](#)

## Videos

[TOP](#)

### Lev-Lok Modular Switch and Receptacle

#### Lev-Lok Modular Switch and Receptacle





Lev-Lok  
Modular Switch



Decora

## ABOUT LEVITON

Leviton is the smart choice, delivering the most comprehensive range of solutions to meet the needs of today's residential, commercial and industrial customers in more than 90 countries across the globe. From simple switches and receptacles, to networking systems and smart home automation, Leviton exceeds market needs by delivering innovative products to create sustainable, intelligent environments through its electrical wiring devices, network and data center connectivity solutions, LED lighting and lighting energy management systems, and security and automation applications. For Leviton, it is clear the FUTURE IS ON.



## PRODUCTS

- Connected Home
- Electric Vehicle Charging
- Electrical Wiring Devices
- GFCIs and AFCIs
- Lighting Controls
- Network Solutions
- Security & Automation
- Submetering
- Surge Protective Devices
- Temporary Power

## SOLUTIONS

- Applications
- Brands
- Business
- Contech Lighting
- Intense Lighting
- Energy Management
- Government
- Home Solutions
- Industrial
- JCC Lighting Products
- Security & Automation

## SUPPORT

- Contact Us
- Cross Reference
- Discussions
- Documents & Resources
- ez-Biz
- ez-Learn
- Knowledgebase
- Leviton Warranties
- Mobile Apps
- Product Support
- Quality Concerns