

## M5362-IG



**Color:**  Orange

UPC Code: 07847736339  
Country Of Origin: Mexico


\*Eligible for ARRA funded projects > \$7,443,000

**NEMA:**  
5-20R



[\\*Disclaimer...](#)

Choose a Color



## M5362-IG

### Brand Features

The Lev-Lok® Modular Wiring Device System is engineered for fast and easy installation. These devices employ a simple twist and lock wiring module that ensures a safe, reliable connection while at the same time providing for extremely fast and easy installation. Lev-Lok brand wiring devices address the reliability and performance concerns of specification engineers without sacrificing the contractor's need for fast, easy installation. Available in extra heavy duty hospital and industrial grades, and heavy duty commercial grade platforms.

### Item Description

20 Amp, 125 Volt, NEMA 5-20R, 2P, 3W, Lev-Lok® Duplex Receptacle, Straight Blade, Industrial Grade, Isolated Ground, Modular Terminals, Plated Steel Strap - ORANGE

### Mating Lev-Lok Wiring Module Required for Use

### Where To Buy

Market Channel

enter your zip code

[Technical Information](#) [Support](#) [Related Products](#) [Videos](#)

## Technical Information

TOP

### AC Horsepower Ratings

**Horsepower Rating:** 1 HP

### Electrical Specifications

**Amperage:** 20 Amp

**Voltage:** 125 Volt

**Pole:** 2

**Wire:** 3

**Dielectric Voltage:** Withstands 2000V per UL498

**Current Limiting:** Full Rated Current

**Temperature Rise:** Max 30C after 250 cycles OL at 200 percent rated current

### Environmental Specifications

**Flammability:** Rated V-2 per UL94

**Operating Temperature:** -40C to 60C

### Material Specifications

**Body Material:** Nylon

**Face Material:** Nylon

**Strap Material:** Galvanized Steel

**Line Contacts:** 0.040" Thick Solid Brass

**Locking Pins:** Solid Brass

**Isolated Ground System:** Brass

### Mechanical Specifications

**Lead Identification:** Leads identified in accordance with UL 498 (black, white & green)

**Product ID:** Markings are permanently marked on device

### Product Features

**NEMA:** 5-20R

**Color:** Orange

### Standards and Certifications

**NEMA:** WD-6

**ANSI:** C-73

**UL 498:** File E13399

**UL Fed Spec WC-596:** File E13399

**CSA C22.2 No. 42:** File 152105

**NOM:** 057

**Warranty:** 10-Year Limited

**RoHS:** Compliant

## Product Lists

[Add to Product List](#)

[View Product List](#)

Quantity:

**Ground Clips:** Brass  
**Shutter Mechanism:** Delrin® Acetal  
**Color:** Orange

## Support

[TOP](#)

[Product Brochure](#)

[Dimensional Data](#)

[Instruction Sheet](#)

[Wiring Diagram](#)

## Related Products

[TOP](#)



**MSTWL-IG**

20 Amp, 125 Volt, 2P, 3W, Wiring Module for Lev-Lok Isolated Ground Receptacles, 6" THHN #12 AWG Stran...  
[More](#)



**84003**

1-Gang Duplex Device Receptacle Wallplate, Standard Size, 430 Stainless Steel, Device Mount, - Sta...  
[More](#)



**LVLOK-TST**

Circuit Analyzer for Lev-Lok Receptacle Modules (MSTWL), cCSAus Listed  
[More](#)



20 Amp, 125 Volt, 2P, 3W, Wiring Module for Lev-Lok Isolated Ground Receptacles, 6" THHN #12 AWG Stran...  
[More](#)

## Videos

[TOP](#)

### Lev-Lok Modular Switch and Receptacle

#### Lev-Lok Modular Switch and Receptacle





## ABOUT LEVITON

Leviton is the smart choice, delivering the most comprehensive range of solutions to meet the needs of today's residential, commercial and industrial customers in more than 90 countries across the globe. From simple switches and receptacles, to networking systems and smart home automation, Leviton exceeds market needs by delivering innovative products to create sustainable, intelligent environments through its electrical wiring devices, network and data center connectivity solutions, LED lighting and lighting energy management systems, and security and automation applications. For Leviton, it is clear the FUTURE IS ON.



## PRODUCTS

- Connected Home
- Electric Vehicle Charging
- Electrical Wiring Devices
- GFCIs and AFCIs
- Lighting Controls
- Network Solutions
- Security & Automation
- Submetering
- Surge Protective Devices
- Temporary Power

## SOLUTIONS

- Applications
- Brands
- Business
- Contech Lighting
- Intense Lighting
- Energy Management
- Government
- Home Solutions
- Industrial
- JCC Lighting Products
- Security & Automation

## SUPPORT

- Contact Us
- Cross Reference
- Discussions
- Documents & Resources
- ez-Biz
- ez-Learn
- Knowledgebase
- Leviton Warranties
- Mobile Apps
- Product Support
- Quality Concerns