

Installation Accessories

Handles



NPT	Poly Handle	Cable Range	Nylon Handle	Poly Handle w/Clamp & Bushing
1/2"	61-3A013-12	.20 - .82	61-3A013	-
3/4"	61-3A013-34	.750 - .875	-	1PM514
1"	61-3A013-1	.875 - 1.000	-	1PM516
1 1/4"	61-3A013-114	1.000 - 1.125	-	1PM518
		1.125 - 1.250	-	1PM520
		1.250 - 1.375	-	1PM522

- Notes:**
- Finger draw plates are recommended for easier connector closure on cord to cord assemblies.
 - For available cord grips, see pgs 171-172.

Angles



Nylon 30° Angle	Metal 30° Angle	Metal Angle FS/FD Box 30°	Metal Straight Adapter
61-3A027	MA2	MAFS2*	MS2

* MAFS2 base measures approximately 4.2" x 2.7". Due to the variation in sizes of FS boxes, please verify that your FS box matches our dimensions, if not call Customer Service for other solutions.

Junction Boxes



NPT	Metal Box	Metal Box with Nylon Angle	Poly* Conduit Entry	Poly 70°** Wall Box	Poly 70° Alum Wall Box
1/2"	MB312	61-3A053-080-12	61-3A023-12	51-BA058	59-BA058-12
3/4"	MB334	61-3A053-080-34	61-3A023-34	51-BA058	59-BA058-34
1"	MB31	61-3A053-080-1	-	51-BA058	59-BA058-1
1 1/4"	MB3114	61-3A053-080-114	-	51-BA058	59-BA058-114
1 1/2"	-	-	-	-	59-BA058-112

- * For poly devices only.
- ** 70° poly boxes are not drilled. Contact customer service if factory drilling is required.
- + Interior volume with receptacle installed.

Miscellaneous Accessories



Finger Drawplates	Protective Cap	Padlockable Plug Cap	Screwdriver for Terminal Screws	Easy Retrofit Adapter Plates	Receptacle Locking Pin
61-3A346	61-3A426	61-3A826	SD18**	see pg 167	LP-843

- * Recommended for cord to cord assembly applications, for easier connector closure.
- ** Requires Padlockable Pawl option (-843) on receptacle.

NPT Guidelines

Cable Range	NPT
.312 - .625	1/2"
.438 - .812	3/4"
.660 - 1.000	1"
.875 - 1.375	1 1/4"

NPT sizes are determined by the cable diameter and third party cord grip.

Accessory Spotlight

Receptacle Locking Pin



A 5/16" locking pin can be ordered to securely lockout receptacles that include the 'padlockable pawl' option. Alternatively the user can utilize a lock with a 5/16" shank. Locks with smaller shanks will NOT securely lockout a receptacle pawl.

Order Example

A typical order should include an inlet part number, a receptacle part number **AND** the matching handles, angles or other required accessories.



Male Inlet with Handle (Plug)
63-38043 + 61-3A013



Female Receptacle with Angle Adapter
63-34043 + 61-3A027