

PUFP Countertop Boxes

CATALOG #	DESCRIPTION
PUFP-CT-B	Brass, pop out counter top plate assembly, with 20 Amp (TR) GFI receptacle
PUFP-CT-B-2USB	Brass, pop out counter top plate assembly, with 15 Amp (TR) single power/2 USB receptacle
PUFP-CT-B-NL	Brass, pop out counter top plate assembly, with 20 Amp (TR) GFI/Night light receptacle
PUFP-CT-BK	Black, pop out counter top plate assembly, with 20 Amp (TR) GFI receptacle
PUFP-CT-BK-2USB	Black, pop out counter top plate assembly, with 15 Amp (TR) single power/2 USB receptacle
PUFP-CT-BK-NL	Black, pop out counter top plate assembly, with 20 Amp (TR) GFI/Night light receptacle
PUFP-CT-R	Red, pop out counter top plate assembly, with 20 Amp (TR) GFI receptacle <i>(Special order product; lead times vary)</i>
PUFP-CT-R-2USB	Red, pop out counter top plate assembly, with 15 Amp (TR) single power/2 USB receptacle <i>(Special order product; lead times vary)</i>
PUFP-CT-R-NL	Red, pop out counter top plate assembly, with 20 Amp (TR) GFI/Night light receptacle <i>(Special order product; lead times vary)</i>
PUFP-CT-SS	Stainless Steel, pop out counter top plate assembly, with 20 Amp (TR) GFI receptacle
PUFP-CT-SS-2USB	Stainless Steel, pop out counter top plate assembly, with 15 Amp (TR) single power/2 USB receptacle
PUFP-CT-SS-NL	Stainless Steel, pop out counter top plate assembly, with 20 Amp (TR) GFI/Night light receptacle
PUFP-CT-WT	White, pop out counter top plate assembly, with 20 Amp (TR) GFI receptacle
PUFP-CT-WT-2USB	White, pop out counter top plate assembly, with 15 Amp (TR) single power/2 USB receptacle
PUFP-CT-WT-NL	White, pop out counter top plate assembly, with 20 Amp (TR) GFI/Night light receptacle

>>>> For PUFP-CT Features and Benefits, see page 6

>>>> All counter top plates 4 7/8 H x 4 3/4 L x 3 1/2 H and include PUFP-WB box



Covers and Boxes PUFP

CATALOG #	DESCRIPTION	DIMENSIONS	
PUFP-B	6" Brass pop out floor plate with 15 Amp (TR) GFI receptacle		
PUFP-BC	6" Brass pop out floor plate with 6-Comm./Data ports		
PUFP-BD	6" Brass pop out floor plate with 15 Amp (TR) decora receptacle		
PUFP-PFC-BRN	6 3/8" Brown plastic pop out floor plate, with 15 Amp (TR) decora receptacle		
PUFP-PFC-GLD	6 3/8" Gold plastic pop out floor plate, with 15 Amp (TR) decora receptacle		
PUFP-S	6" Stainless steel pop out floor plate with 15 Amp (TR) GFI receptacle		
PUFP-SC	6" Stainless steel pop out floor plate with 6-Comm./Data ports		
PUFP-SD	6" Stainless steel pop out floor plate with 15 Amp (TR) decora receptacle		
PUFP-LRA	Leveling ring for PUFP plates		
PUFP-LRA-HT	Leveling ring adapter for PUFP plates and Hubbell or T&B box		
CATALOG #	DESCRIPTION	A (WIDTH)	B (HEIGHT)
PUFP-HB	Concrete box for PUFP plates	4 5/16"	3 1/4"
PUFP-WB	Wood floor box for PUFP plates	3 7/8"	3 1/8"
FB	PVC floor box (must use in conjunction with PUFP-LRA to mount cover); box UL listed #514C	5"	6"

PUFP-B



PUFP-BC



PUFP-BD



FEATURES & BENEFITS (PAGES 5 & 6)

- UL recognized** 498, 514A, 943, 1059, and NEC 210.52(C).
CUL recognized 22.2 #'s 42, 158, and 18.1-04.
- Pops up** when in use
- Hides in the box** when not in use
- Complies with **NEC code 406.5(E)** for use in countertops
- For **residential or commercial** applications
- Installs in **concrete or wood** floors
- Scrub water tight** construction
- All PUFP style supplied with **tamper resistant receptacles**

PUFP-PFC-BRN



PUFP-PFC-GLD



PUFP-S



PUFP-SC



PUFP-SD



125V ~20A; Conforms to UL STD.514A and 498; Certified to CSA STD.C22.2.; No.18.1-04 and 42-M1984; LEW ELECTRIC FITTINGS CO

* ETL listing excludes PUFP-PFC-BRN; PUFP-PFC-GLD

PUFP-LRA



PUFP-LRA-HT



PUFP-HB



PUFP-WB



FB

